




FEATURES:

- Cable enables BNC based test instruments to interface to banana jacks.
- Banana plugs can be stacked on top or side of the banana plugs for additional test versatility.
- BNC connector, wire breakout and banana plugs are molded directly to the cable for added pull strength.

MATERIALS:

BNC: Body: Brass, Nickel Plated, Center Pin: Brass, Gold Plated, Impedance: 50 Ohms

Strain Relief: PVC, Color: Black

Cable: RG58C/U, Impedance: 50 Ohms Nom., Cap. (pF/Ft). 30.8, O.D. .195" (5,0 mm) Nom., Color: Black

Marking: "POMONA 5268-C-XX"

Molded Breakout: PVC, Color: Black

Breakout Leads: 20 AWG, Stranding 41 x 36 t.c., PVC Insulated, .087" (2,21mm) O.D.

Banana Plugs: Body – Brass, Nickel Plated

Spring – Beryllium Copper, Nickel Plated

Insulation – Polypropylene, Color: One Black, One Red

RATING:

Operating Temperature: 50°C (+122°F) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500 WVDC Max.

ORDERING INFORMATION: Model 5268-C-XX

XX = Cable Length Std. Lengths: 12" (30,5 cm), 24" (60,96 cm), 36" (91,44 cm), 48" (121,92 cm) & 60" (152,40 cm). Additional lengths can be quoted upon request.

Ordering Example: 5268-C-36 , Cable length will be 36" (91,44 cm) long.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5268-C-48](#) [5268-C-36](#) [5268-C-24](#) [5268-C-60](#)