

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: TIN, 80-100 μ "

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20M Ω Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000M Ω

Min.


Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
06	2.54	18.31
08	3.81	19.58
10	5.08	20.85
12	6.35	22.12
14	7.62	23.39
16	8.89	24.66
18	10.16	25.93
20	11.42	27.20
24	13.97	29.74
26	15.24	31.01
30	17.78	33.55
34	20.32	36.09
40	24.13	39.90
50	30.48	46.25
60	36.83	52.60
64	39.37	55.14

CnC Tech,LLC





3210-XX-003-12-99

SCALE SHEET UNIT



UNLESS TOLERANCE
GENERAL ANGLE
X. ± 0.30 X.' $\pm 3.0^\circ$
.X ± 0.20 .X' $\pm 2.0^\circ$
.XX ± 0.15 .XX' $\pm 1.0^\circ$
.XXX ± 0.08 .XXX $\pm 0.5^\circ$

DRAW BY
DESIGN BY
CHECK BY
APPROVE BY



P.C.B LAYOUT