

[PRODUCT SEARCH](#) [NEW PRODUCTS](#) [DESIGN GUIDE](#) [CUSTOMER SERVICE](#) [CROSS-REFERENCE](#) [DISTRIBUTORS & REPS.](#) [TECHNICAL ASSISTANCE](#) [CHECK STOCK](#)

[HOME](#) [PLANT TOUR](#) [ABOUT US](#) [QUALITY ASSURANCE](#) [ORDER FREE SAMPLES](#) [MY CARTS](#) [DISTRIBUTOR LOGIN](#)

MILL-MAX MAXIMUM CONNECTIONS




Home > Product Search > [Product Details](#)

PRODUCT DETAILS



Product Number: 110-XX-XXX-41-530000



DESCRIPTION:

DIP Socket
Military DIP Socket; MIL-S-83734
Standard Solder Tail (0.125 Tail)
Open Frame
Through Hole

MATES WITH:

[142-XX-XXX-XX-XXXXXX](#)
[151-XX-XXX-00-009000](#)
[151-XX-XXX-00-010000](#)
[151-XX-XXX-00-011000](#)
[153-XX-XXX-00-001000](#)

LOOSE PIN INFORMATION:

Loose Pin Used=[1001](#)
Material=[Brass Alloy](#)

INSULATOR INFORMATION:

[PCT](#) High Temperature

CONTACT:

[30](#)=Standard 4 Finger Contact
Current Rating=3 Amps
Material=[Beryllium Copper](#)

PACKAGING:

Packaged in Tubes

For Additional plating options click [here](#)
All dimensions above are in inches, for metric dimensions click [here](#).

Want to modify this part? Email Technical Services with your application specific requirement.

Plating Code

[33](#)

Shell Plating

30 μ " Gold MIN. over 100 μ " Nickel
300 μ " (60/40)Tin/Lead over 50 μ " Nickel
300 μ " (60/40)Tin/Lead over 50 μ " Nickel

Inner Contact Plating

30 μ " Gold MIN. over 50 μ " Nickel
30 μ " Gold MIN.
100 μ " Tin/Lead over 50 μ " Nickel

Narrow your search

How many Pin Positions do you require?

Plating Options:


All dimensions in inches unless otherwise noted.

# Of Pins	A	B	C	Qty. per Tube	Military Part Number	Mill-Max Part Number	Free Sample Cart	Availability ☐ Show In Stock Items Only	RoHS Compliant	Datasheet
8	0.4	0.3	0.4	50	M83734/2-028	110- 33 -308-41-530000	N/A	In Stock at Distributor	NO	
14	0.7	0.3	0.4	28	M83734/3-028	110- 33 -314-41-530000	N/A	In Stock at Factory. Contact Distributor for Quote	NO	
16	0.8	0.3	0.4	25	M83734/4-028	110- 33 -316-41-530000	N/A	In Stock at Distributor	NO	

18	0.9	0.3	0.4	22	M83734/5-028	110-33-318-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
20	1.0	0.3	0.4	20	M83734/13-028	110-33-320-41-530000	N/A	In Stock at Distributor	NO	
22	1.1	0.4	0.5	18	M83734/6-028	110-33-422-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
24	1.2	0.6	0.7	16	M83734/8-028	110-33-624-41-530000	N/A	In Stock at Factory. Contact Distributor for Quote	NO	
28	1.4	0.6	0.7	14	M83734/7-028	110-33-628-41-530000	N/A	In Stock at Distributor	NO	
40	2.0	0.6	0.7	10	M83734/10-028	110-33-640-41-530000	N/A	In Stock at Factory. Contact Distributor for Quote	NO	
48	2.4	0.6	0.7	8	M83734/14-028	110-33-648-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
64	3.2	0.9	1.0	6	M83734/15-028	110-33-964-41-530000	N/A	In Stock at Factory. Contact Distributor for Quote	NO	
8	0.4	0.3	0.4	50	M83734/2-029	110-83-308-41-530000	N/A	In Stock at Distributor	NO	
14	0.7	0.3	0.4	28	M83734/3-029	110-83-314-41-530000	N/A	In Stock at Distributor	NO	
16	0.8	0.3	0.4	25	M83734/4-029	110-83-316-41-530000	N/A	In Stock at Distributor	NO	
18	0.9	0.3	0.4	22	M83734/5-029	110-83-318-41-530000	N/A	In Stock at Distributor	NO	
20	1.0	0.3	0.4	20	M83734/13-029	110-83-320-41-530000	N/A	In Stock at Distributor	NO	
22	1.1	0.4	0.5	18	M83734/6-029	110-83-422-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
24	1.2	0.6	0.7	16	M83734/8-029	110-83-624-41-530000	N/A	In Stock at Distributor	NO	
28	1.4	0.6	0.7	14	M83734/7-029	110-83-628-41-530000	N/A	In Stock at Distributor	NO	
40	2.0	0.6	0.7	10	M83734/10-029	110-83-640-41-530000	N/A	In Stock at Distributor	NO	
48	2.4	0.6	0.7	8	M83734/14-029	110-83-648-41-530000	N/A	In Stock at Distributor	NO	
64	3.2	0.9	1.0	6	M83734/15-029	110-83-964-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
8	0.4	0.3	0.4	50	M83734/2-030	110-88-308-41-530000	N/A	In Stock at Distributor	NO	
14	0.7	0.3	0.4	28	M83734/3-030	110-88-314-41-530000	N/A	In Stock at Distributor	NO	
16	0.8	0.3	0.4	25	M83734/4-030	110-88-316-41-530000	N/A	In Stock at Distributor	NO	
18	0.9	0.3	0.4	22	M83734/5-030	110-88-318-41-530000	N/A	In Stock at Distributor	NO	
20	1.0	0.3	0.4	20	M83734/13-030	110-88-320-41-530000	N/A	Contact Distributor for Price and Delivery	NO	


22	1.1	0.4	0.5	18	M83734/6-030	110-88-422-41-530000	N/A	In Stock at Distributor	NO	
24	1.2	0.6	0.7	16	M83734/8-030	110-88-624-41-530000	N/A	In Stock at Distributor	NO	
28	1.4	0.6	0.7	14	M83734/7-030	110-88-628-41-530000	N/A	In Stock at Distributor	NO	
40	2.0	0.6	0.7	10	M83734/10-030	110-88-640-41-530000	N/A	In Stock at Distributor	NO	
48	2.4	0.6	0.7	8	M83734/14-030	110-88-648-41-530000	N/A	Contact Distributor for Price and Delivery	NO	
64	3.2	0.9	1.0	6	M83734/15-030	110-88-964-41-530000	N/A	Contact Distributor for Price and Delivery	NO	

Recently Viewed Products




223-XX-XXX-41-101000

DIP Socket
Military DIP Socket; MIL-S-83734
3 Level Wrapost Tail



223-XX-XXX-41-101000

DIP Socket
Military DIP Socket; MIL-S-83734
3 Level Wrapost Tail



223-XX-XXX-41-101000

DIP Socket
Military DIP Socket; MIL-S-83734
3 Level Wrapost Tail

[TOP OF PAGE](#)