



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDFMilitary Sta ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'GE52-C'

Your search criteria matched only one product, shown below

GE52-C



|  |                              |                                                               |
|--|------------------------------|---------------------------------------------------------------|
|  | Part Number                  | GE52-C                                                        |
|  | RoHS Compliancy Status       | Compliant                                                     |
|  | Part Description             | Military Specification Nylon Grommet Edging in 12.75" strips. |
|  | Material                     | Nylon 6.6                                                     |
|  | Color                        | Natural                                                       |
|  | Military Specification       | MS21266-1N                                                    |
|  | Height (In.)                 | .16                                                           |
|  | Height (mm)                  | 3.9                                                           |
|  | Length (In.)                 | 12.75                                                         |
|  | Length (mm)                  | 323.9                                                         |
|  | Width (In.)                  | .15                                                           |
|  | Width (mm)                   | 3.8                                                           |
|  | CE Compliant                 | No                                                            |
|  | CE Marking                   | No                                                            |
|  | Flammability Rating          | UL94 V-2                                                      |
|  | Outside Depth (In.)          | .155                                                          |
|  | Outside Depth (mm)           | 3.9                                                           |
|  | Outside Width (In.)          | .150                                                          |
|  | Outside Width (mm)           | 3.8                                                           |
|  | Panel Thickness Range (In.)  | .015 – .052                                                   |
|  | Panel Thickness Range (mm)   | 0.4 – 1.3                                                     |
|  | Pricing Description          | Grommet Edging, Slot Strip, Nylon, Natural                    |
|  | Temperature Range            | -40°F to 149°F (-40°C to 65°C)                                |
|  | Min. Order UOM               | PC                                                            |
|  | Min. Order Qty.              | 100                                                           |
|  | BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                |
|  | Add to Favorite Product List |                                                               |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.