


# IEEE 1394 Firewire, 6 Pin Receptacle Right Angle (SMT)

154-FWR41-E

**KOBI**CONN

IEEE 1394 Firewire, 6 Pin Receptacle Right Angle (SMT)

154-FWR41-E



Dimensions: mm (In.)

| MATERIALS              |                                 |
|------------------------|---------------------------------|
| Withstanding Voltage:  | DC 500 ±50V                     |
| Insulation Resistance: | 100 Megaohms min.               |
| Contact Resistance:    | 30 Milliohms max.               |
| Housing:               | High Temperature Thermoplastics |
| Shell:                 | Copper Alloy                    |
| Contacts:              | Copper Alloy                    |
| RoHS Compliant         |                                 |

Date Last Revised: 6/13/12

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300999

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-FWR41-E](#)