


ALL DIMENSIONS ARE IN (mm)											
Part Number	Wire Size	Wire Class	Wire Strip Length	*UL Listed Stud Hole Diameter Size Range (1 or 2 Stud Holes)	$l \pm 2.76$	$o \pm .50$	$i \pm .50$	$a \pm 2.25$	c	b	t
LCMDX10-00-Q	10 mm ²	5f & 6f	16.0	5.50 - 11.0	81.2	7.20	5.50	14.5	62.7±1.25	15.0±1.25	1.10±.40
LCMDX16-00-Q	16 mm ²	5f & 6f	16.5	5.50 - 11.0	89.5	9.52	7.14	15.0	70.5±1.25	20.0±1.25	1.60±.40
LCMDX25-00-Q	25 mm ²	5f & 6f	19.0	6.60 - 11.0	92.5	10.40	8.20	17.5	70.5±2.25	21.5±2.25	1.50±.40
LCMDX35-00-Q	35 mm ²	5f & 6f	21.8	6.60 - 14.0	94.5	12.30	9.80	20.3	69.5±2.25	23.0±2.25	1.80±.40
LCMDX50-00-X	50 mm ²	5f & 6f	24.8	6.60 - 14.0	98.0	14.20	11.50	23.3	70.5±2.25	20.8±2.25	2.80±.40
LCMDX70-00-X	70 mm ²	5f & 6f	26.0	6.60 - 14.0	105.0	16.50	13.50	24.5	73.0±2.25	24.5±2.25	2.90±.40
LCMDX95-00-X	95 mm ²	5f & 6f	26.0	9.0 - 18.0	109.5	18.60	15.20	24.5	74.5±2.25	27.5±2.25	3.40±.45
LCMDX120-00-X	120 mm ²	5f & 6f	29.0	9.0 - 18.0	118.5	21.00	16.50	27.5	83.0±2.25	30.5±2.25	4.30±.45
LCMDX150-00-X	150 mm ²	5f & 6f	29.7	9.0 - 22.0	121.5	23.00	18.60	28.2	83.0±2.25	33.5±2.25	4.40±.50
LCMDX185-00-X	185 mm ²	5f & 6f	36.5	11.0 - 22.0	131.0	26.00	20.80	35.0	85.0±2.25	37.5±2.25	5.20±.50
LCMDX240-00-5	240 mm ²	5f & 6f	41.8	11.0 - 22.0	139.0	29.00	23.50	40.3	86.5±2.25	42.5±2.25	5.30±.55
LCMDX300-00-5	300 mm ²	5f	46.3	11.0 - 22.0	151.5	33.00	26.20	44.8	94.5±2.25	48.0±2.25	6.70±.55



- NOTES:
1. Material: High conductivity seamless copper tube.
 2. Plating: Parts are annealed and tin plated.
 3. WireType: Class 5 and 6 Flexible Stranded Copper Conductor per DIN VDE 0295, IEC 60228, and HD 383.
 4. UL Listed & CSA Certified Wire Connectors for applications up to 35kv, when crimped per instruction sheet included with Panduit packaging. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
 5. UL & CSA Temperature Rating: 90°C
 6. *Stud holes to be centered along the centerline of the tongue (palm).



										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										METRIC FLEX LUGS - LCMDX SERIES 10-300mm ² BLANK TONGUE CUSTOMER DRAWING			
										UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
										DRAWN BY TLCO	MAT'L: SEE NOTES ABOVE	SCALE NONE	
00	11/12	TLCO	TLCO	DRAWING RELEASED		10N014BD-NC	RGB	RGB	DATE 5/11	DRAWING NO / CAD FILE		DWG B SIZE	
REV	DATE	BY	CHK	DESCRIPTION		ECN	-R	SUP	CHK'D TLCO	10N014BD-NC			