




D

C

B

A







NOTES:

- △ PLATING: 0,5µm MIN. TIN OVER NICKEL.
- △ PLATING:

PARTNUMBER	PERFORMANCE LEVEL
1551099-1	PERFORMANCE LEVEL 1: CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III: UNCONTROLLED ENVIRONMENT APPLICATIONS. SEE PRODUCT SPEC 108-19353
1551099-2	PERFORMANCE LEVEL 2: CONFORMS TO ALL TESTING ACCORDING PRODUCT SPEC 108-19320, -250 MATING CYCLES, 4 DAYS MIXED GAS TEST PER IEC 60068-2-60 METHOD I

- 3 CONSULT APPLICATION SPEC OR CONTACT TE CONNECTIVITY FOR PERMISSIBLE CONTACT ASSIGNMENTS.
- △ 4 BLACK SQUARE MARKING FOR LEVEL 4 PIN AT POSITION a12 AS INDICATED.
- △ 5 CONNECTOR MARKED WITH PARTNUMBER AND DATE CODE.
- 6 FOR PC-BOARD ROUTING RECOMMENDATIONS SEE SPEC 114-19140



PRODUCT HAS NOT COMPLETED
QUALIFICATION TESTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Vathsa 09-Feb-2009	
DIMENSIONS: mm		CHK R. Annokkee 09-Feb-2009	
		APVD Mark Westen 09-Feb-2009	
		PRODUCT SPEC SEE NOTE 2	
MATERIAL -		APPLICATION SPEC 114-19106	
		WEIGHT -	
		CUSTOMER DRAWING	

3	OVERMOLD	LCP 30% GF NATURAL	
2	HOUSING	LCP 30% GF NATURAL	
1	CONTACT	COPPER ALLOY	
ITEM NO.	DESCRIPTION	MATERIAL	

NAME MALE CONNECTOR Z-PACK Slim UHD			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1551099	-
SCALE 5:1		SHEET 1 OF 1	REV A