

datasheet for MA 1
article number: 930317801

product description:	order number: 930 317-801
description:	Miniature alligator clip with high strength insulation and nickel-plated brass/bronze jaws. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. Capable of clamping flat components (soldering eyes) and wire up to a maximum diameter of 4mm.
typ:	MA 1 rot / red
system:	2mm system
order number:	930 317-801
clamping range:	4 mm
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	clamp
type of termination:	2 mm socket (spring-loaded)
rated voltage:	30 VAC / 60 VDC
rated current: Please consider derating curve!	8 A
contact resistance:	10 mOhm
material	
contact material:	brass / bronze
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +100 °C
flammable class:	
housing (basic material):	UL 94 HB
drawing	