



High-Performance 8-Bit Microcontrollers

Z8 Encore! XP™ 4K Series with eXtended Peripherals

Product Brief

PB013602-0304

PRELIMINARY

Z8  **Encore!**

Product Block Diagram

1–4KB Flash	256B–1KB RAM	16B–128B NVDS	Up to 8 Channels 10-Bit ADC
Two 16-Bit Timers/PWM	20MHz eZ8 CPU		Trans-Impedance Amplifier
Watch-Dog Timer with RC Oscillator			POR/VBO & Reset Control
UART with IrDA	On-Chip Debugger	Crystal/RC Oscillator	
Temperature Sensor	Analog Comparator	Internal Precision Oscillator	
Up to 25 General-Purpose I/O Pins			

Overview

The Z8 Encore! XP™ 4K Series devices are Flash microcontrollers based on the ZiLOG eZ8 CPU. The Z8 Encore! XP™ 4K Series MCU family of devices sets a new standard for performance and on-chip peripherals.

The Z8 Encore! XP™ 4K Series devices support up to 4KB of Flash program memory and 1KB register RAM

The Z8 Encore! XP™ 4K Series devices feature up to eight single-ended/differential channels of 10-bit A/D conversion with 1x or 20x differential input gain and a transimpedance amplifier for current measurement.

An on-chip temperature sensor allows die temperature measurement over a range of -40° to $+105^{\circ}\text{C}$

These devices include two enhanced 16-bit timer blocks featuring PWMs and Capture and Compare.

Up to 18 vectored interrupts with programmable priorities provide increased application flexibility.

The Z8 Encore! XP™ 4K Series features an on-chip Internal Precision Oscillator (5MHz/32KHz) as a trimmable clock source that requires no external components.

The new single-pin debugger and programming interface simplifies code development and allows for easy in-circuit programming.

The full-duplex UART provides serial communications and IrDA encoding and decoding capability.

Features

- 20MHz eZ8 CPU core
- Up to 4KB Flash memory with in-circuit programming capability
- Up to 1KB register RAM
- Up to 128B nonvolatile data storage
- Up to 8 channels 10-bit analog-to-digital converter (ADC)
- On-chip temperature sensor
- On-chip analog comparator
- On-chip transimpedance (current sense) amplifier
- Full-duplex 9-bit UART with bus transceiver Driver Enable Control
- Infrared Data Association (IrDA)-compliant infrared encoder/decoders



- Two 16-bit timers with capture, compare, and PWM capability
- Watch-Dog Timer (WDT) with internal RC oscillator
- 17–25 I/O pins depending upon package
- Up to 18 interrupts with configurable priority
- On-Chip Debugger
- Voltage Brown-Out Protection (VBO)
- Power-On Reset (POR)
- Internal Precision Oscillator (5MHz/32KHz)
- Crystal oscillator with three power settings and external RC network option
- 2.7–3.6V operating voltage with 5V-tolerant inputs
- 20- and 28-pin packages
- 0° to +70°C standard temperature and –40° to +105°C extended temperature operating ranges

eZ8 CPU Features

- New instructions for improved performance including BIT, BSWAP, BTJ, CPC, LDC, LDCI, LEA, MULT, and SRL
- New instructions support 12-bit linear addressing of the Register File
- Compatible with existing Z8® code
- Up to 10 MIPS operation
- C-Compiler friendly
- 2–9 clock cycles per instruction

Z8 Encore! XP™ 4K Series Development Kit

The Z8 Encore! XP™ 4K Series Development Kit includes the following:

Hardware

- Z8 Encore! XP™ 4K Series Development board
- Smart Cable for PC to Z8 Encore! XP™ 4K Series Development board (DB9 to 6-pin male)
- 5VDC power supply

Software on CD-ROM

- ZDS II–Z8 Encore!® IDE with ANSI C-Compiler
- Sample code
- Document browser
- Acrobat Reader® install program

Documentation

- Quick Start Guide
- Registration card
- Z8 Encore! XP™ 4K Series technical documentation (on CD-ROM)
 - Development Kit User Manual
 - ZDSII IDE User Manual
 - eZ8 CPU User Manual
 - Product specification
 - Product brief
 - Application notes

Architecture

Figure 1 illustrates the Z8 Encore! XP™ 4K Series block diagram.




Figure 1. Z8 Encore! XP™ 4K Series Block Diagram



Ordering Information

Order the Z8 Encore! XP™ 4K Series from ZiLOG®, referencing the following part numbers. For more information regarding ordering, please consult your local ZiLOG® sales office. The ZiLOG® website at www.zilog.com lists all regional offices and provides additional Z8 Encore!® product information.

Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 4KB Flash, 10-Bit Analog-to-Digital Converter											
Standard Temperature: 0° to 70°C											
Z8F042ASH020SC	4KB	1KB	128B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F042AHH020SC	4KB	1KB	128B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F042APH020SC	4KB	1KB	128B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F042ASJ020SC	4KB	1KB	128B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F042AHJ020SC	4KB	1KB	128B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F042APJ020SC	4KB	1KB	128B	23	18	2	8	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F042ASH020EC	4KB	1KB	128B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F042AHH020EC	4KB	1KB	128B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F042APH020EC	4KB	1KB	128B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F042ASJ020EC	4KB	1KB	128B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F042AHJ020EC	4KB	1KB	128B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F042APJ020EC	4KB	1KB	128B	23	18	2	8	1	1	1	PDIP 28-pin package



Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 4KB Flash											
Standard Temperature: 0° to 70°C											
Z8F041ASH020SC	4KB	1KB	128B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F041AHH020SC	4KB	1KB	128B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F041APH020SC	4KB	1KB	128B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F041ASJ020SC	4KB	1KB	128B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F041AHJ020SC	4KB	1KB	128B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F041APJ020SC	4KB	1KB	128B	25	17	2	0	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F041ASH020EC	4KB	1KB	128B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F041AHH020EC	4KB	1KB	128B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F041APH020EC	4KB	1KB	128B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F041ASJ020EC	4KB	1KB	128B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F041AHJ020EC	4KB	1KB	128B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F041APJ020EC	4KB	1KB	128B	25	17	2	0	1	1	1	PDIP 28-pin package



Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 2KB Flash, 10-Bit analog-to-Digital Converter											
Standard Temperature: 0° to 70°C											
Z8F022ASH020SC	2KB	512B	64B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F022AHH020SC	2KB	512B	64B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F022APH020SC	2KB	512B	64B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F022ASJ020SC	2KB	512B	64B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F022AHJ020SC	2KB	512B	64B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F022APJ020SC	2KB	512B	64B	23	18	2	8	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F022ASH020EC	2KB	512B	64B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F022AHH020EC	2KB	512B	64B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F022APH020EC	2KB	512B	64B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F022ASJ020EC	2KB	512B	64B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F022AHJ020EC	2KB	512B	64B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F022APJ020EC	2KB	512B	64B	23	18	2	8	1	1	1	PDIP 28-pin package



Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 2KB Flash											
Standard Temperature: 0° to 70°C											
Z8F021ASH020SC	2KB	512B	64B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F021AHH020SC	2KB	512B	64B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F021APH020SC	2KB	512B	64B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F021ASJ020SC	2KB	512B	64B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F021AHJ020SC	2KB	512B	64B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F021APJ020SC	2KB	512B	64B	25	17	2	0	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F021ASH020EC	2KB	512B	64B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F021AHH020EC	2KB	512B	64B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F021APH020EC	2KB	512B	64B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F021ASJ020EC	2KB	512B	64B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F021AHJ020EC	2KB	512B	64B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F021APJ020EC	2KB	512B	64B	25	17	2	0	1	1	1	PDIP 28-pin package




Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 1KB Flash, 10-Bit Analog-to-Digital Converter											
Standard Temperature: 0° to 70°C											
Z8F012ASH020SC	1KB	256B	16B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F012AHH020SC	1KB	256B	16B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F012APH020SC	1KB	256B	16B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F012ASJ020SC	1KB	256B	16B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F012AHJ020SC	1KB	256B	16B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F012APJ020SC	1KB	256B	16B	23	18	2	8	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F012ASH020EC	1KB	256B	16B	17	18	2	7	1	1	1	SOIC 20-pin package
Z8F012AHH020EC	1KB	256B	16B	17	18	2	7	1	1	1	SSOP 20-pin package
Z8F012APH020EC	1KB	256B	16B	17	18	2	7	1	1	1	PDIP 20-pin package
Z8F012ASJ020EC	1KB	256B	16B	23	18	2	8	1	1	1	SOIC 28-pin package
Z8F012AHJ020EC	1KB	256B	16B	23	18	2	8	1	1	1	SSOP 28-pin package
Z8F012APJ020EC	1KB	256B	16B	23	18	2	8	1	1	1	PDIP 28-pin package



Part Number	Flash	RAM	NVDS	I/O Lines	Interrupts	16-Bit Timers w/PWM	10-Bit A/D Channels	UART with IrDA	Comparator	Temperature Sensor	Description
Z8 Encore! XP™ with 1KB Flash											
Standard Temperature: 0° to 70°C											
Z8F011ASH020SC	1KB	256B	16B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F011AHH020SC	1KB	256B	16B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F011APH020SC	1KB	256B	16B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F011ASJ020SC	1KB	256B	16B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F011AHJ020SC	1KB	256B	16B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F011APJ020SC	1KB	256B	16B	25	17	2	0	1	1	1	PDIP 28-pin package
Extended Temperature: -40° to 105°C											
Z8F011ASH020EC	1KB	256B	16B	17	17	2	0	1	1	1	SOIC 20-pin package
Z8F011AHH020EC	1KB	256B	16B	17	17	2	0	1	1	1	SSOP 20-pin package
Z8F011APH020EC	1KB	256B	16B	17	17	2	0	1	1	1	PDIP 20-pin package
Z8F011ASJ020EC	1KB	256B	16B	25	17	2	0	1	1	1	SOIC 28-pin package
Z8F011AHJ020EC	1KB	256B	16B	25	17	2	0	1	1	1	SSOP 28-pin package
Z8F011APJ020EC	1KB	256B	16B	25	17	2	0	1	1	1	PDIP 28-pin package
Z8F04A28100KIT											Development Kit



Part Number Suffix Designations



Disclaimer

©2004 by ZiLOG, Inc. All rights reserved. Information in this publication concerning the devices, applications, or technology described is intended to suggest possible uses and may be superseded. ZiLOG, INC. DOES NOT ASSUME LIABILITY FOR OR PROVIDE A REPRESENTATION OF ACCURACY OF THE INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED IN THIS DOCUMENT. ZiLOG ALSO DOES NOT ASSUME LIABILITY FOR INTELLECTUAL PROPERTY INFRINGEMENT RELATED IN ANY MANNER TO USE OF INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED HEREIN OR OTHERWISE. Devices sold by ZiLOG, Inc. are covered by warranty and limitation of liability provisions appearing in the ZiLOG, Inc. Terms and Conditions of Sale. ZiLOG, Inc. makes no warranty of merchantability or fitness for any purpose. Except with the express written approval of ZiLOG, use of information, devices, or technology as critical components of life support systems is not authorized. No licenses are conveyed, implicitly or otherwise, by this document under any intellectual property rights.