





3D VIEW



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI5921	27JUL1997	-	JEN
	A	REVISED PER E.O. PI6266	07SEP1999	-	-
	AI	REVISED PER PCN-25-253066	19JUN2025	UBF	CB

4


MATERIAL: RECEPTACLE & CAP: PA66 GF15, BLACK
WEDGELOCK (INCLUDED): PBT GF30 (GREEN)
BUSBAR: COPPER ALLOY, NICKEL PLATED.

3. THE 12 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 76 AMPS.

2

ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.

1. THIS DT04-12PB-P021 MATES WITH DT06-12SB-XXXX (XXXX = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. GONZALEZ	20AUG1999	 TE Connectivity		
		CHK -	07SEP1999			
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DT 12 WAY REC KEY ARRANGEMENT -B- 12 PIN BUSBAR-NICKEL PLATED COLOR: BLACK		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.025 [0.63] 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-151009		
				APPLICATION SPEC 114-151009		
MATERIAL - 4				WEIGHT 26g	SIZE A3	CAGE CODE 00779
				CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
					DRAWING NO C-DT04-12PB-P021	RESTRICTED TO -
					REV AI	