







| CKT. SIZE | DIM. A REF. |       | DIM. B REF. |       |
|-----------|-------------|-------|-------------|-------|
|           | (MM)        | INCH  | (MM)        | INCH  |
| 4         | (2.54)      | .100  | (4.83)      | .190  |
| 6         | (5.08)      | .200  | (7.37)      | .290  |
| 8         | (7.62)      | .300  | (9.91)      | .390  |
| 10        | (10.16)     | .400  | (12.45)     | .490  |
| 12        | (12.70)     | .500  | (14.99)     | .590  |
| 14        | (15.24)     | .600  | (17.53)     | .690  |
| 16        | (17.78)     | .700  | (20.07)     | .790  |
| 18        | (20.32)     | .800  | (22.61)     | .890  |
| 20        | (22.86)     | .900  | (25.15)     | .990  |
| 22        | (25.40)     | 1.000 | (27.69)     | 1.090 |
| 24        | (27.94)     | 1.100 | (30.23)     | 1.190 |
| 26        | (30.48)     | 1.200 | (32.77)     | 1.290 |
| 28        | (33.02)     | 1.300 | (35.31)     | 1.390 |
| 30        | (35.56)     | 1.400 | (37.85)     | 1.490 |
| 32        | (38.10)     | 1.500 | (40.39)     | 1.590 |
| 34        | (40.64)     | 1.600 | (42.93)     | 1.690 |
| 36        | (43.18)     | 1.700 | (45.47)     | 1.790 |
| 38        | (45.72)     | 1.800 | (48.01)     | 1.890 |
| 40        | (48.26)     | 1.900 | (50.55)     | 1.990 |
| 42        | (50.80)     | 2.000 | (53.09)     | 2.090 |
| 44        | (53.34)     | 2.100 | (55.63)     | 2.190 |
| 46        | (55.88)     | 2.200 | (58.17)     | 2.290 |
| 48        | (58.42)     | 2.300 | (60.71)     | 2.390 |
| 50        | (60.96)     | 2.400 | (63.25)     | 2.490 |
| 52        | (63.50)     | 2.500 | (65.79)     | 2.590 |
| 54        | (66.04)     | 2.600 | (68.33)     | 2.690 |
| 56        | (68.58)     | 2.700 | (70.87)     | 2.790 |
| 58        | (71.12)     | 2.800 | (73.41)     | 2.890 |
| 60        | (73.66)     | 2.900 | (75.95)     | 2.990 |
| 62        | (76.20)     | 3.000 | (78.49)     | 3.090 |
| 64        | (78.74)     | 3.100 | (81.03)     | 3.190 |
| 66        | (81.28)     | 3.200 | (83.57)     | 3.290 |
| 68        | (83.82)     | 3.300 | (86.11)     | 3.390 |
| 70        | (86.36)     | 3.400 | (88.65)     | 3.490 |
| 72        | (88.90)     | 3.500 | (91.19)     | 3.590 |
| 74        | (91.44)     | 3.600 | (93.73)     | 3.690 |
| 76        | (93.98)     | 3.700 | (96.27)     | 3.790 |
| 78        | (96.52)     | 3.800 | (98.81)     | 3.890 |
| 80        | (99.06)     | 3.900 | (101.35)    | 3.990 |

NOTES:

- 1 - PIN PUSHOUT FORCE: 4 LBS. MINIMUM
  - 2 - FOR ILLUSTRATION PURPOSES, 20 (DUAL 10) CIRCUIT SIZE IS SHOWN.
  - 3 - PINS MUST MEET SOLDERABILITY SPEC. ES-152, EXCEPT VOIDS ARE PERMISSIBLE AT BANDOLIER PIN FAYING SURFACE. (APPROX. .025 LNG X .006 WD. REF.) - 2 LOCATIONS
  - 4 - WAFER TO BE FLAT WITHIN (0.03 MM/CM)/.003 IN./IN.
  - 5 - MEASURE POINT FOR PLATING THICKNESS.
  - 6 - THIS PRODUCT CONFORMS TO MOLEX PRODUCT SPEC. PS-70203.
  - 7 - FOR ASSEMBLIES WITH VOIDS, REFER TO DRAWING NUMBER SDA-70203-5001-9999.
  - 8 - PACKAGING INFORMATION: (UNLESS OTHERWISE NOTED IN TABLES)
- | CIRCUIT SIZE | PACKAGING DRAWING |
|--------------|-------------------|
| 4 THROUGH 8  | PK-70873-0353     |
| 10 AND OVER  | PK-70873-0075     |

FINISH:

- TIN - .000150 MINIMUM TIN PLATE OVER NICKEL PLATE.
  - 15 GOLD - .000015 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER NICKEL PLATE OVERALL.
  - 30 GOLD - .000030 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER NICKEL PLATE OVERALL.
- \*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO ROHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.

MATERIAL:

- WAFER - G.F. POLYESTER; 94V-0; COLOR: BLACK
- PIN - PHOSPHOR BRONZE

|    |                                                     |
|----|-----------------------------------------------------|
| D  | LEAD FREE<br>UCP2004-1770<br>RWHITE 04/04/23        |
| CI | REVISE PKNG<br>ECN UDT2000-0949<br>SCHAFFER 00/4/6  |
| C  | REVISED<br>PER ECN # U60711<br>1/8/96 BJS/RCB       |
| BI | ADDED EDP #S<br>PER ECR # U60256<br>95/08/23 CAC    |
| B  | VOIDED EDP NO'S<br>PER ECR # U60097<br>95/07/27 CAC |
| A  | RELEASED<br>PER ECR # U31656<br>11/18/93 REED       |

|   |   |
|---|---|
| 2 | D |
| 1 | D |

|      |     |      |      |           |
|------|-----|------|------|-----------|
| MFG. | SH. | REV. | LTR. | REVISIONS |
|------|-----|------|------|-----------|

|                                                                                            |  |                                                                                                                       |  |
|--------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------|--|
| DIMENSIONS SHOWN (METRIC) INCH<br>UNLESS OTHERWISE SPECIFIED<br>TOLERANCES: ANGULAR ± 1/2° |  | ▽ = 0<br>= 0<br>REVISIONS ONLY ON CAD SYSTEM                                                                          |  |
| TITLE<br>SALES ASSY-DUAL ROW<br>WAFER W/BREAK-OFF OPTION<br>RIGHT ANGLE/.025 SQ PINS       |  | SHEET NO. DATE<br>1 OF 2 11/18/93                                                                                     |  |
| PART NO.<br>SEE CHART<br>SDA-70203-0001-5000                                               |  | DRWG. NO.<br>SDA-70203-0001-5000                                                                                      |  |
| FILE NAME<br>570203X1                                                                      |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  |
| DRWG. BY<br>SMR                                                                            |  | CHKD. BY<br>SMR                                                                                                       |  |
| APPR. BY                                                                                   |  | SCALE<br>4: 1                                                                                                         |  |

| I3 |                                  | I2                            |              | I1               |                      | I0         |              | 9          |              | 8                               |                                                                                            | 7                  |                                                    | 6          |                                                                                                                                            | 70203          |  | 4 |  | 3 |  | 2 |  | 1 |  |
|----|----------------------------------|-------------------------------|--------------|------------------|----------------------|------------|--------------|------------|--------------|---------------------------------|--------------------------------------------------------------------------------------------|--------------------|----------------------------------------------------|------------|--------------------------------------------------------------------------------------------------------------------------------------------|----------------|--|---|--|---|--|---|--|---|--|
| J  | ENGINEERING<br>NUMBER<br>A-70203 | RELEASE<br>FOR<br>MANUFACTURE |              | EXPOSED PIN DIM. |                      |            |              |            |              | PLATING<br>PER NOTES<br>SHEET 1 | CONNECTOR END PLATING                                                                      |                    | P.C. BOARD END PLATING                             |            | FOR PKG.<br>INFO. SEE<br>NOTE 8,<br>SHEET 1                                                                                                |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              | C<br>REF.        | D<br>±(0.25)<br>.010 |            |              | TYPE       | E<br>MEAS.   |                                 | TYPE                                                                                       | G<br>MEAS.         |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 |                                                                                            |                    |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
|    | -0001/-0039                      | R.F.M.                        |              | (2.79)<br>.110   | (6.10)<br>.240       |            |              |            |              | TIN                             | TIN                                                                                        | (2.54)<br>.100     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
| I  | -0040/-0078                      | R.F.M.                        |              | (2.79)<br>.110   | (8.13)<br>.320       |            |              |            |              | TIN                             | TIN                                                                                        | (4.57)<br>.180     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
|    | -0079/-0117                      | R.F.M.                        |              | (4.45)<br>.175   | (6.10)<br>.240       |            |              |            |              | TIN                             | TIN                                                                                        | (2.54)<br>.100     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
|    | -0157/-0195                      | R.F.M.                        |              | (2.79)<br>.110   | (6.10)<br>.240       |            |              |            |              | 15 GOLD                         | GOLD                                                                                       | (2.54)<br>.100     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
| H  | -0196/-0234                      | R.F.M.                        |              | (2.79)<br>.110   | (8.13)<br>.320       |            |              |            |              | 15 GOLD                         | GOLD                                                                                       | (4.57)<br>.180     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
|    | -0313/-0351                      | R.F.M.                        |              | (2.79)<br>.110   | (6.10)<br>.240       |            |              |            |              | 30 GOLD                         | GOLD                                                                                       | (2.54)<br>.100     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
|    | -0352/-0390                      | R.F.M.                        |              | (2.79)<br>.110   | (8.13)<br>.320       |            |              |            |              | 30 GOLD                         | GOLD                                                                                       | (4.57)<br>.180     |                                                    | TIN        | (1.27)<br>.050                                                                                                                             |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 |                                                                                            |                    |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
| G  | CKTS                             | EDP NUMBER                    | ENG NUMBER   | EDP NUMBER       | ENG NUMBER           | EDP NUMBER | ENG NUMBER   | EDP NUMBER | ENG NUMBER   | EDP NUMBER                      | ENG NUMBER                                                                                 | EDP NUMBER         | ENG NUMBER                                         | EDP NUMBER | ENG NUMBER                                                                                                                                 | CKTS           |  |   |  |   |  |   |  |   |  |
|    | 04                               | 10-88-1045                    | A-70203-0001 | 10-88-1046       | A-70203-0040         |            |              | 10-89-1046 | A-70203-0157 | 10-89-1047                      | A-70203-0196                                                                               | 10-89-2046         | A-70203-0313                                       | 10-89-2047 | A-70203-0352                                                                                                                               | 04             |  |   |  |   |  |   |  |   |  |
|    | 06                               | 10-88-1065                    | A-70203-0002 | 10-88-1066       | A-70203-0041         |            |              | 10-89-1066 | A-70203-0158 | 10-89-1067                      | A-70203-0197                                                                               | 10-89-2066         | A-70203-0314                                       | 10-89-2067 | A-70203-0353                                                                                                                               | 06             |  |   |  |   |  |   |  |   |  |
| F  | 08                               | 10-88-1085                    | A-70203-0003 | 10-88-1086       | A-70203-0042         |            |              | 10-89-1086 | A-70203-0159 | 10-89-1087                      | A-70203-0198                                                                               | 10-89-2086         | A-70203-0315                                       | 10-89-2087 | A-70203-0354                                                                                                                               | 08             |  |   |  |   |  |   |  |   |  |
|    | 10                               | 10-88-1105                    | A-70203-0004 | 10-88-1106       | A-70203-0043         |            |              | 10-89-1106 | A-70203-0160 | 10-89-1107                      | A-70203-0199                                                                               | 10-89-2106         | A-70203-0316                                       | 10-89-2107 | A-70203-0355                                                                                                                               | 10             |  |   |  |   |  |   |  |   |  |
|    | 12                               | 10-88-1125                    | A-70203-0005 | 10-88-1126       | A-70203-0044         |            |              | 10-89-1126 | A-70203-0161 | 10-89-1127                      | A-70203-0200                                                                               | 10-89-2126         | A-70203-0317                                       | 10-89-2127 | A-70203-0356                                                                                                                               | 12             |  |   |  |   |  |   |  |   |  |
| E  | 14                               | 10-88-1145                    | A-70203-0006 | 10-88-1146       | A-70203-0045         |            |              | 10-89-1146 | A-70203-0162 | 10-89-1147                      | A-70203-0201                                                                               | 10-89-2146         | A-70203-0318                                       | 10-89-2147 | A-70203-0357                                                                                                                               | 14             |  |   |  |   |  |   |  |   |  |
|    | 16                               | 10-88-1165                    | A-70203-0007 | 10-88-1166       | A-70203-0046         |            |              | 10-89-1166 | A-70203-0163 | 10-89-1167                      | A-70203-0202                                                                               | 10-89-2166         | A-70203-0319                                       | 10-89-2167 | A-70203-0358                                                                                                                               | 16             |  |   |  |   |  |   |  |   |  |
|    | 18                               | 10-88-1185                    | A-70203-0008 | 10-88-1186       | A-70203-0047         |            |              | 10-89-1186 | A-70203-0164 | 10-89-1187                      | A-70203-0203                                                                               | 10-89-2186         | A-70203-0320                                       | 10-89-2187 | A-70203-0359                                                                                                                               | 18             |  |   |  |   |  |   |  |   |  |
| D  | 20                               | 10-88-1205                    | A-70203-0009 | 10-88-1206       | A-70203-0048         |            |              | 10-89-1206 | A-70203-0165 | 10-89-1207                      | A-70203-0204                                                                               | 10-89-2206         | A-70203-0321                                       | 10-89-2207 | A-70203-0360                                                                                                                               | 20             |  |   |  |   |  |   |  |   |  |
|    | 22                               | 10-88-1225                    | A-70203-0010 | 10-88-1226       | A-70203-0049         |            |              | 10-89-1226 | A-70203-0166 | 10-89-1227                      | A-70203-0205                                                                               | 10-89-2226         | A-70203-0322                                       | 10-89-2227 | A-70203-0361                                                                                                                               | 22             |  |   |  |   |  |   |  |   |  |
|    | 24                               | 10-88-1245                    | A-70203-0011 | 10-88-1246       | A-70203-0050         |            |              | 10-89-1246 | A-70203-0167 | 10-89-1247                      | A-70203-0206                                                                               | 10-89-2246         | A-70203-0323                                       | 10-89-2247 | A-70203-0362                                                                                                                               | 24             |  |   |  |   |  |   |  |   |  |
| C  | 26                               | 10-88-1265                    | A-70203-0012 | 10-88-1266       | A-70203-0051         |            |              | 10-89-1266 | A-70203-0168 | 10-89-1267                      | A-70203-0207                                                                               | 10-89-2266         | A-70203-0324                                       | 10-89-2267 | A-70203-0363                                                                                                                               | 26             |  |   |  |   |  |   |  |   |  |
|    | 28                               | 10-88-1285                    | A-70203-0013 | 10-88-1286       | A-70203-0052         |            |              | 10-89-1286 | A-70203-0169 | 10-89-1287                      | A-70203-0208                                                                               | 10-89-2286         | A-70203-0325                                       | 10-89-2287 | A-70203-0364                                                                                                                               | 28             |  |   |  |   |  |   |  |   |  |
|    | 30                               | 10-88-1305                    | A-70203-0014 | 10-88-1306       | A-70203-0053         |            |              | 10-89-1306 | A-70203-0170 | 10-89-1307                      | A-70203-0209                                                                               | 10-89-2306         | A-70203-0326                                       | 10-89-2307 | A-70203-0365                                                                                                                               | 30             |  |   |  |   |  |   |  |   |  |
| B  | 32                               | 10-88-1325                    | A-70203-0015 | 10-88-1326       | A-70203-0054         |            |              | 10-89-1326 | A-70203-0171 | 10-89-1327                      | A-70203-0210                                                                               | 10-89-2326         | A-70203-0327                                       | 10-89-2327 | A-70203-0366                                                                                                                               | 32             |  |   |  |   |  |   |  |   |  |
|    | 34                               | 10-88-1345                    | A-70203-0016 | 10-88-1346       | A-70203-0055         |            |              | 10-89-1346 | A-70203-0172 | 10-89-1347                      | A-70203-0211                                                                               | 10-89-2346         | A-70203-0328                                       | 10-89-2347 | A-70203-0367                                                                                                                               | 34             |  |   |  |   |  |   |  |   |  |
|    | 36                               | 10-88-1365                    | A-70203-0017 | 10-88-1366       | A-70203-0056         |            |              | 10-89-1366 | A-70203-0173 | 10-89-1367                      | A-70203-0212                                                                               | 10-89-2366         | A-70203-0329                                       | 10-89-2367 | A-70203-0368                                                                                                                               | 36             |  |   |  |   |  |   |  |   |  |
| A  | 38                               | 10-88-1385                    | A-70203-0018 | 10-88-1386       | A-70203-0057         |            |              | 10-89-1386 | A-70203-0174 | 10-89-1387                      | A-70203-0213                                                                               | 10-89-2386         | A-70203-0330                                       | 10-89-2387 | A-70203-0369                                                                                                                               | 38             |  |   |  |   |  |   |  |   |  |
|    | 40                               | 10-88-1405                    | A-70203-0019 | 10-88-1406       | A-70203-0058         |            |              | 10-89-1406 | A-70203-0175 | 10-89-1407                      | A-70203-0214                                                                               | 10-89-2406         | A-70203-0331                                       | 10-89-2407 | A-70203-0370                                                                                                                               | 40             |  |   |  |   |  |   |  |   |  |
|    | 42                               | 10-88-1425                    | A-70203-0020 | 10-88-1426       | A-70203-0059         |            |              | 10-89-1426 | A-70203-0176 | 10-89-1427                      | A-70203-0215                                                                               | 10-89-2426         | A-70203-0332                                       | 10-89-2427 | A-70203-0371                                                                                                                               | 42             |  |   |  |   |  |   |  |   |  |
| Z  | 44                               | 10-88-1445                    | A-70203-0021 | 10-88-1446       | A-70203-0060         |            |              | 10-89-1446 | A-70203-0177 | 10-89-1447                      | A-70203-0216                                                                               | 10-89-2446         | A-70203-0333                                       | 10-89-2447 | A-70203-0372                                                                                                                               | 44             |  |   |  |   |  |   |  |   |  |
|    | 46                               | 10-88-1465                    | A-70203-0022 | 10-88-1466       | A-70203-0061         |            |              | 10-89-1466 | A-70203-0178 | 10-89-1467                      | A-70203-0217                                                                               | 10-89-2466         | A-70203-0334                                       | 10-89-2467 | A-70203-0373                                                                                                                               | 46             |  |   |  |   |  |   |  |   |  |
|    | 48                               | 10-88-1485                    | A-70203-0023 | 10-88-1486       | A-70203-0062         |            |              | 10-89-1486 | A-70203-0179 | 10-89-1487                      | A-70203-0218                                                                               | 10-89-2486         | A-70203-0335                                       | 10-89-2487 | A-70203-0374                                                                                                                               | 48             |  |   |  |   |  |   |  |   |  |
| Y  | 50                               | 10-88-1505                    | A-70203-0024 | 10-88-1506       | A-70203-0063         |            |              | 10-89-1506 | A-70203-0180 | 10-89-1507                      | A-70203-0219                                                                               | 10-89-2506         | A-70203-0336                                       | 10-89-2507 | A-70203-0375                                                                                                                               | 50             |  |   |  |   |  |   |  |   |  |
|    | 52                               | 10-88-1525                    | A-70203-0025 | 10-88-1526       | A-70203-0064         |            |              | 10-89-1526 | A-70203-0181 | 10-89-1527                      | A-70203-0220                                                                               | 10-89-2526         | A-70203-0337                                       | 10-89-2527 | A-70203-0376                                                                                                                               | 52             |  |   |  |   |  |   |  |   |  |
|    | 54                               | 10-88-1545                    | A-70203-0026 | 10-88-1546       | A-70203-0065         |            |              | 10-89-1546 | A-70203-0182 | 10-89-1547                      | A-70203-0221                                                                               | 10-89-2546         | A-70203-0338                                       | 10-89-2547 | A-70203-0377                                                                                                                               | 54             |  |   |  |   |  |   |  |   |  |
| X  | 56                               | 10-88-1565                    | A-70203-0027 | 10-88-1566       | A-70203-0066         |            |              | 10-89-1566 | A-70203-0183 | 10-89-1567                      | A-70203-0222                                                                               | 10-89-2566         | A-70203-0339                                       | 10-89-2567 | A-70203-0378                                                                                                                               | 56             |  |   |  |   |  |   |  |   |  |
|    | 58                               | 10-88-1585                    | A-70203-0028 | 10-88-1586       | A-70203-0067         |            |              | 10-89-1586 | A-70203-0184 | 10-89-1587                      | A-70203-0223                                                                               | 10-89-2586         | A-70203-0340                                       | 10-89-2587 | A-70203-0379                                                                                                                               | 58             |  |   |  |   |  |   |  |   |  |
|    | 60                               | 10-88-1605                    | A-70203-0029 | 10-88-1606       | A-70203-0068         |            |              | 10-89-1606 | A-70203-0185 | 10-89-1607                      | A-70203-0224                                                                               | 10-89-2606         | A-70203-0341                                       | 10-89-2607 | A-70203-0380                                                                                                                               | 60             |  |   |  |   |  |   |  |   |  |
| W  | 62                               | 10-88-1625                    | A-70203-0030 | 10-88-1626       | A-70203-0069         |            |              | 10-89-1626 | A-70203-0186 | 10-89-1627                      | A-70203-0225                                                                               | 10-89-2626         | A-70203-0342                                       | 10-89-2627 | A-70203-0381                                                                                                                               | 62             |  |   |  |   |  |   |  |   |  |
|    | 64                               | 10-88-1645                    | A-70203-0031 | 10-88-1646       | A-70203-0070         |            |              | 10-89-1646 | A-70203-0187 | 10-89-1647                      | A-70203-0226                                                                               | 10-89-2646         | A-70203-0343                                       | 10-89-2647 | A-70203-0382                                                                                                                               | 64             |  |   |  |   |  |   |  |   |  |
|    | 66                               | 10-88-1665                    | A-70203-0032 | 10-88-1666       | A-70203-0071         |            |              | 10-89-1666 | A-70203-0188 | 10-89-1667                      | A-70203-0227                                                                               | 10-89-2666         | A-70203-0344                                       | 10-89-2667 | A-70203-0383                                                                                                                               | 66             |  |   |  |   |  |   |  |   |  |
| V  | 68                               | 10-88-1685                    | A-70203-0033 | 10-88-1686       | A-70203-0072         |            |              | 10-89-1686 | A-70203-0189 | 10-89-1687                      | A-70203-0228                                                                               | 10-89-2686         | A-70203-0345                                       | 10-89-2687 | A-70203-0384                                                                                                                               | 68             |  |   |  |   |  |   |  |   |  |
|    | 70                               | 10-88-1705                    | A-70203-0034 | 10-88-1706       | A-70203-0073         |            |              | 10-89-1706 | A-70203-0190 | 10-89-1707                      | A-70203-0229                                                                               | 10-89-2706         | A-70203-0346                                       | 10-89-2707 | A-70203-0385                                                                                                                               | 70             |  |   |  |   |  |   |  |   |  |
|    | 72                               | 10-88-1725                    | A-70203-0035 | 10-88-1726       | A-70203-0074         |            |              | 10-89-1726 | A-70203-0191 | 10-89-1727                      | A-70203-0230                                                                               | 10-89-2726         | A-70203-0347                                       | 10-89-2727 | A-70203-0386                                                                                                                               | 72             |  |   |  |   |  |   |  |   |  |
| U  | 74                               | 10-88-1745                    | A-70203-0036 | 10-88-1746       | A-70203-0075         |            |              | 10-89-1746 | A-70203-0192 | 10-89-1747                      | A-70203-0231                                                                               | 10-89-2746         | A-70203-0348                                       | 10-89-2747 | A-70203-0387                                                                                                                               | 74             |  |   |  |   |  |   |  |   |  |
|    | 76                               | 10-88-1765                    | A-70203-0037 | 10-88-1766       | A-70203-0076         |            |              | 10-89-1766 | A-70203-0193 | 10-89-1767                      | A-70203-0232                                                                               | 10-89-2766         | A-70203-0349                                       | 10-89-2767 | A-70203-0388                                                                                                                               | 76             |  |   |  |   |  |   |  |   |  |
|    | 78                               | 10-88-1785                    | A-70203-0038 | 10-88-1786       | A-70203-0077         |            |              | 10-89-1786 | A-70203-0194 | 10-89-1787                      | A-70203-0233                                                                               | 10-89-2786         | A-70203-0350                                       | 10-89-2787 | A-70203-0389                                                                                                                               | 78             |  |   |  |   |  |   |  |   |  |
| T  | 80                               | 10-88-1805                    | A-70203-0039 | 10-88-1806       | A-70203-0078         | 10-88-1807 | A-70203-0117 | 10-89-1806 | A-70203-0195 | 10-89-1807                      | A-70203-0234                                                                               | 10-89-2806         | A-70203-0351                                       | 10-89-2807 | A-70203-0390                                                                                                                               | 80             |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 |                                                                                            |                    |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 |                                                                                            |                    |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
| S  |                                  |                               |              |                  |                      |            |              |            |              |                                 | DIMENSIONS SHOWN (METRIC) INCH<br>UNLESS OTHERWISE SPECIFIED<br>TOLERANCES: ANGULAR ± 1/2° |                    | ▽ = 0   ▽ = 0   REVISE ONLY ON CAD SYSTEM          |            | TITLE<br>SALES ASSY-DUAL ROW<br>WAFER W/BREAK-OFF OPTION<br>RIGHT ANGLE/.025 SQ PINS                                                       |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 | INCH   METRIC<br>3 PLACE ± .005   ---<br>2 PLACE ± .01   ± 0.13<br>1 PLACE ---   ± 0.25    |                    | MOLEX INCORPORATED<br>LITELILL, ILL. 60532 U.S.A.  |            | SHEET NO. 2   DATE 11/18/93                                                                                                                |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              |                                 | DRAFT WHERE APPLICABLE MUST<br>REMAIN WITHIN DIMENSIONS                                    |                    | PART NO. SEE CHART   DRWG. NO. SDA-70203-0001-5000 |            | FILE NAME S70203X2   THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              | DRWG. BY SMR   CHK'D BY SMR     |                                                                                            | SCALE :            |                                                    | APP'D. BY  |                                                                                                                                            | DIV. SIZE DA C |  |   |  |   |  |   |  |   |  |
|    |                                  |                               |              |                  |                      |            |              |            |              | L.T.R.   REVISIONS              |                                                                                            | L.T.R.   REVISIONS |                                                    |            |                                                                                                                                            |                |  |   |  |   |  |   |  |   |  |
| I3 |                                  | I2                            |              | I1               |                      | I0         |              | 9          |              | 8                               |                                                                                            | 7                  |                                                    | 6          |                                                                                                                                            | 5              |  | 4 |  | 3 |  | 2 |  | 1 |  |