

AZ2850


RELAY ORDERING DATA

COIL SPECIFICATIONS – DC Coil				ORDER NUMBER*
Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Coil Resistance $\pm 10\%$	
6	4.5	10.5	22	AZ2850-2C-6D
12	9.0	20.7	86	AZ2850-2C-12D
24	18.0	41.8	350	AZ2850-2C-24D
48	36.0	83.4	1390	AZ2850-2C-48D
110	82.5	190.5	7255	AZ2850-2C-110D

COIL SPECIFICATIONS – AC Coil 60 Hz [1]					ORDER NUMBER*
Nominal Coil VAC	Must Operate VAC	Max. Continuous VAC	Nominal Current mA $\pm 10\%$	Coil Resistance $\pm 10\%$	
12	9.6	15.6	325	9.5	AZ2850-2C-12A
24	19.2	31.2	154	35.7	AZ2850-2C-24A
120	96.0	156.0	33.5	830	AZ2850-2C-120A
208	166.4	270.4	19.3	2600	AZ2850-2C-208A
220	176.0	286	18.1	2870	AZ2850-2C-220A
240	192.0	312.0	17.3	3800	AZ2850-2C-240A
277	221.6	360.1	14.5	4700	AZ2850-2C-277A

*Add suffix "E" for epoxy sealed version. Substitute "2A" for "2C" to indicate DPST (N.O.) contacts. Add suffix "E" to "2A" or "2C" to indicate AgSNO₂ contacts [1] For 50 Hz coil replace "A" with "A5" (example: "A2280-2C-24A5").

MECHANICAL DATA



Dimensions in inches with metric equivalents in parentheses. Tolerance: $\pm .010$ "



AMERICAN ZETTLER, INC.

www.azettler.com

75 COLUMBIA • ALISO VIEJO, CA 92656 • PHONE: (949) 831-5000 • FAX: (949) 831-8642 • E-MAIL: SALES@AZETTLER.COM

3/3/08W