

▶ Hexagonal crimping dies

Hexagonal crimping dies

▷ Crimp conforms to NFC 20-130.

- For crimping pliers 985913.

	Die mm²	To NFC20130
985914	6	•
985915	10	•
985916	16	•
985917	25	•
985918	35	•
985919	50	•
985920	70	•
985921	95	•
985922	120	•
985923	150	•



▶ Crimping pliers for open-barrel connectors

Crimping pliers for open-barrel connectors

985757

- 1.5 to 6 mm².

	L mm	ΔΔ g
985757	195	250




▶ Crimping pliers for cable terminals

Maintenance crimping pliers for cable terminals

985895

- Complies with NFC 63-023.
- Stainless steel dies
- 5 patterns :
pattern no. 1 : 0.5 - 0.75 - 1 mm²
pattern no. 2 : 1.5 mm²
pattern no. 3 : 2.5 mm²
pattern no. 4 : 4 mm²
pattern no. 5 : 6 mm²
- Release catch always accessible.
- Soft feel.
- Ergonomic design for enhanced grip.
- Reverse crimping : terminal placed in the fixed jaw for greater efficiency and precision.

	Capacity Ø mm²	L mm	ΔΔ g
985895	0,5 → 6	230	490



Self-adjusting crimping pliers for cable terminals

985898

- Crimps : 0.14 - 0.25 - 0.5 - 0.75 - 1 - 1.5 - 2.5 - 4 - 6 mm².
- Ratchet system guarantees a secure crimp.
- Complies with NFC 63-023.
- Easy release in the event of incorrect operation.
- Comfortable grips.

	L mm	ΔΔ g
985898	210	500

