

1 Outlet, Direct Plug-In, 350 Joules, Timer - Protect It! Surge Suppressor

MODEL NUMBER: **SK10TG**



Highlights

- 1 outlets/direct plug-in
- 350 joule rating
- Timer selection switch for 1, 3, or 6 hours
- Diagnostic LEDs
- \$5,000 Ultimate Lifetime Insurance (USA & Canada only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection

Package Includes

- SK10TG surge suppressor
- Instruction sheet

Description

The SK10TG surge suppressor with timer offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 1 outlet and 350 joules of surge energy absorption. Timer selection switch for 1, 3, or 6 hours helps make connected devices more energy efficient. On/Off push button lets you shut off outlet at any time. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 1 outlets / direct plug-in
- Surge suppression rating: 350 joules
- Timer Feature
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1875
Circuit Breaker (amps)	15
Outlet quantity / type	1 NEMA 5-15P

Outlet Type	NEMA 5-15P
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input connection type	NEMA 5-15P input plug
Input plug features	120V, 15A
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
UPC ASSIGNMENT	
Unit Carton UPC#	037332148308
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	350
AC suppression response time	< 1ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping voltage (RMS)	400
AC suppression surge current rating	27,000
UL1449 let through rating	500, 400, 500
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	2.76 x 2.76 x 1.50
Unit Dimensions (HWD/cm)	7 x 7 x 3.8
Unit weight (lbs)	.22
Unit weight (kg)	.10
Material of construction	Plastic
Integrated keyhole mounting tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black
Receptacle Color	Black
Style	Direct plug-in

CERTIFICATIONS

UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS

WARRANTY

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[SK10TG](#)