


## Lamp Specification

| Wamco Part No. | Envelope Size | Base Type | Rating   | Filament Shape |
|----------------|---------------|-----------|----------|----------------|
| WL-1309        | B-6           | BA15s     | 28V .52A | 2C2R           |

| Test Volts | Current (A) |      |      | Light Output (MSCP) |      |      | Life Hours |
|------------|-------------|------|------|---------------------|------|------|------------|
|            | Min.        | Nom. | Max. | Min.                | Nom. | Max. |            |
| 28         | .468        | .520 | .572 | 12                  | 15   | 18   | 300 Hrs    |

### Dimensional Characteristics:

1. L.C.L. = 1.06" (26.9mm)
2. Base = Nickel-plated Brass Construction.
3. Spiral Filament Supports.



### Title:

**B-6 Single Contact Bayonet Base Lamp  
28V .52A Gas-Filled**

|          |         |    |                                                                     |
|----------|---------|----|---------------------------------------------------------------------|
| Drawn    | 7/19/00 | CI | Notes:<br>Unless otherwise specified, all dimensions are in inches. |
| Checked  | 7/19/00 | GM |                                                                     |
| Approved | 7/19/00 | GM |                                                                     |