


3M™ Pak 50 Wiremount Socket

.050" Wiremount Socket for .050" Pitch Cable

P50 Series



- P50 connector terminates two separate 1.27 mm (50 mil) pitch flat ribbon cables
- Accepts 28 AWG PVC cable (3M 3365 Series)
- Latch/eject mechanism maintains a secure connection
- Cable strain relief standard
- Tooling available for customer cable assembly termination
- RoHS* compliant

Date Modified: December 15, 2006

TS-1163-05
Sheet 1 of 2

Physical

Insulation

Material: Glass filled Nylon

Flammability: UL 94V-0

Color: Black

Contact

Material: Copper Alloy

Plating

Underplating: Nickel

Wiping Area: .25 μ m [10 μ "] Gold

Termination Area: Gold Flash

Wire Accomodation: 28 AWG Stranded PVC Flat Ribbon Cable

Electrical

Current Rating: 0.5 A

Insulation Resistance: 10^3 M Ω min. at 500 V DC

Withstanding Voltage 650 V AC for 1 minute

Environmental

Temperature Rating: -55°C to +85°C

RoHS compliant means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated in writing by 3M, this information represents 3M's knowledge and belief based on information provided by third party suppliers to 3M.

UL File No.: E68080

3M

Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

800-225-5373

3M™ Pak 50 Wiremount Socket

.050" Wiremount Socket for .050" Pitch Cable

P50 Series





Product Table / Dimensions

Contact Quantity	A	B	C	D
20	25.43	17.83	15.43	11.43
	[1.001]	[0.702]	[0.607]	[0.450]
26	29.24	21.64	19.24	15.24
	[1.151]	[0.852]	[0.757]	[0.600]
30	31.78	24.18	21.78	17.78
	[1.251]	[0.952]	[0.857]	[0.700]
32	33.05	25.45	23.05	19.05
	[1.301]	[1.002]	[0.907]	[0.750]
34	34.32	26.72	24.32	20.32
	[1.351]	[1.052]	[0.957]	[0.800]

Contact Quantity	A	B	C	D
40	38.13	30.53	28.13	24.13
	[1.501]	[1.202]	[1.107]	[0.950]
50	44.48	36.88	34.48	30.48
	[1.751]	[1.452]	[1.357]	[1.200]
52	45.75	38.15	35.75	31.75
	[1.801]	[1.502]	[1.407]	[1.250]
60	50.83	43.23	40.83	36.83
	[2.001]	[1.702]	[1.607]	[1.450]
68	55.91	48.31	45.91	41.91
	[2.201]	[1.902]	[1.807]	[1.650]



X-X' Cross Section



"n" is number of contacts

Note: Strain relief standard.

Ordering Information

P50 - XXXS - EA

Contact Quantity
See Table

Application tools: 3640 press (or equivalent), 3443-128 locator platen, 3442-126 platen.

TS-1163-05
Sheet 2 of 2

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



3M Electronics

6801 River Place Blvd.
Austin, TX 78726-9000
800/225-5373
www.3M.com/electronics

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%
Post-Consumer Fiber

Printed in USA.

© 3M 2006

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[P50-050S-EA](#) [P50-030S-EA](#) [P50-026S-EA](#) [P50-068S-EA](#) [P50-060S-EA](#) [P50-052S-EA](#)