



### 322 R

#### Reversible screwdriver for slot-head and PHILLIPS® screws

- Ergonomic bimaterial grip
- Chrome Vanadium steel blade
- Chrome plated finish with sandblasted tip

| axbxc<br>mm | n°xc | L<br>mm | code     |   |
|-------------|------|---------|----------|---|
| 1x6x75      | 2x75 | 200     | 03220097 | 1 |




### 323 RV

#### Empty holders for screwdrivers

- For screwdrivers 322-324
- Enamelled sheet steel

| n° | L<br>mm | code    |   |
|----|---------|---------|---|
| 7  | 205     | Q323511 | 1 |
| 10 | 295     | Q323512 | 1 |
| 13 | 390     | Q323513 | 1 |



### 324

UNI 10562 ISO 2380 DIN 5264

#### Screwdrivers for slot-head screws

- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc<br>mm | L<br>mm | code     |   |
|-------------|---------|----------|---|
| 0,5x3x75    | 169     | 03240001 | 5 |
| 0,5x3x100   | 194     | 03240002 | 5 |
| 0,8x4x100   | 204     | 03240003 | 5 |
| 0,8x4x125   | 229     | 03240004 | 5 |
| 0,8x4x150   | 254     | 03240005 | 5 |
| 1x5,5x100   | 209     | 03240006 | 5 |
| 1x5,5x125   | 234     | 03240007 | 5 |
| 1x5,5x150   | 259     | 03240008 | 5 |
| 1,2x6,5x125 | 245     | 03240009 | 5 |
| 1,2x6,5x150 | 270     | 03240010 | 5 |
| 1,2x8x200   | 325     | 03240011 | 5 |
| 1,6x10x200  | 325     | 03240012 | 5 |
| 2x12x250    | 375     | 03240013 | 1 |




### 324 SE6

#### Set of six screwdrivers for slot-head screws

- 324 D/0,4x2,5x50-0,5x3x75-0,6x3,5x100
- 324/0,8x4x100-1x5,5x125-1,2x6,5x150

| g   | code     |   |
|-----|----------|---|
| 460 | 03240252 | 1 |




### 324 D

UNI 10562 ISO 2380 DIN 5264

#### Screwdrivers for slot-head screws

- For driving recessed studs or screws
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc<br>mm | L<br>mm | code     |   |
|-------------|---------|----------|---|
| 0,4x2,5x50  | 144     | 03240026 | 5 |
| 0,5x3x75    | 169     | 03240027 | 5 |
| 0,6x3,5x100 | 204     | 03240028 | 5 |
| 0,8x4x100   | 204     | 03240029 | 5 |
| 0,8x4x150   | 254     | 03240030 | 1 |
| 1x5,5x125   | 234     | 03240031 | 5 |
| 1x5,5x150   | 259     | 03240032 | 1 |
| 1,2x6,5x150 | 270     | 03240033 | 1 |




### 324 E

UNI 10562 ISO 2380 DIN 5264

#### Screwdrivers for slot-head screws

- Model with hexagonal drive and hexagonal blade for powerful tightening, also with a wrench
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc<br>mm | L<br>mm | code     |   |
|-------------|---------|----------|---|
| 0,8x4x100   | 204     | 03240116 | 1 |
| 1x5,5x125   | 234     | 03240117 | 1 |
| 1,2x6,5x150 | 270     | 03240096 | 1 |
| 1,2x8x175   | 300     | 03240097 | 1 |
| 1,6x8x175   | 300     | 03240098 | 1 |
| 1,6x10x175  | 300     | 03240099 | 1 |
| 2x12x250    | 375     | 03240100 | 1 |




### 324 L

UNI 10562 ISO 2380 DIN 5264

#### Screwdrivers for slot-head screws

- Model with long blade
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc<br>mm | L<br>mm | code     |   |
|-------------|---------|----------|---|
| 0,6x3,5x250 | 354     | 03240019 | 1 |
| 0,8x4x300   | 404     | 03240020 | 1 |
| 1x5,5x300   | 409     | 03240021 | 1 |



### 324 PH

UNI ISO 8764 DIN 5260

#### Screwdrivers for Phillips® screws

- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L<br>mm | code     |   |
|-------|---------|----------|---|
| 0x75  | 179     | 03240039 | 5 |
| 1x75  | 184     | 03240040 | 5 |
| 1x100 | 209     | 03240041 | 5 |
| 2x100 | 220     | 03240042 | 5 |
| 2x125 | 245     | 03240043 | 5 |
| 3x150 | 275     | 03240044 | 5 |
| 4x200 | 325     | 03240045 | 1 |




### 324 PH/SE4

#### Set of four screwdrivers for slot-head and PHILLIPS® screws

- 324 PH/0x75-1x75-2x100-3x150

| n°xa | L mm     | code |  |
|------|----------|------|--|
| 530  | 03240268 | 1    |  |




### 324 EPH

UNI ISO 8764 DIN 5260

#### Screwdrivers for Phillips® screws

- Model with hexagonal drive and hexagonal blade for powerful tightening, also with a wrench
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L mm | mm | code     |   |
|-------|------|----|----------|---|
| 1x100 | 209  | 8  | 03240121 | 1 |
| 2x125 | 245  | 10 | 03240104 | 1 |
| 3x150 | 275  | 12 | 03240105 | 1 |
| 4x200 | 325  | 14 | 03240106 | 1 |




### 324 LPH

UNI ISO 8764 DIN 5260

#### Screwdrivers for Phillips® screws

- Model with long blade
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L mm | code     |   |
|-------|------|----------|---|
| 1x250 | 359  | 03240050 | 5 |
| 2x250 | 370  | 03240051 | 5 |




### 324 PZ

UNI ISO 8764 DIN 5260

#### Screwdrivers for POZIDRIV®-SUPADRIV® screws

- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L mm | code     |   |
|-------|------|----------|---|
| 0x75  | 179  | 03240056 | 1 |
| 1x75  | 184  | 03240057 | 1 |
| 2x100 | 220  | 03240058 | 1 |
| 3x150 | 275  | 03240059 | 1 |




### 324 EPZ

UNI ISO 8764 DIN 5260

#### Screwdrivers for POZIDRIV®-SUPADRIV® screws

- Model with hexagonal drive and hexagonal blade for powerful tightening, also with a wrench
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L mm | mm | code     |   |
|-------|------|----|----------|---|
| 2x125 | 245  | 10 | 03240110 | 1 |
| 3x150 | 275  | 12 | 03240111 | 1 |
| 4x200 | 325  | 14 | 03240112 | 1 |




### 324 N

UNI 10562 ISO 2380 DIN 5264

#### Screwdrivers for slot-head screws

- Stubby model
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc mm   | L mm | code     |   |
|------------|------|----------|---|
| 0,8x4x35   | 91   | 03240063 | 5 |
| 1x5,5x35   | 91   | 03240064 | 5 |
| 1,2x6,5x35 | 91   | 03240065 | 5 |



### 324 NPH

UNI ISO 8764 DIN 5260

#### Screwdrivers for Phillips® screws

- Stubby model
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa | L mm | code     |   |
|------|------|----------|---|
| 1x35 | 91   | 03240068 | 5 |
| 2x35 | 91   | 03240069 | 5 |



### 324 SH8

#### Set of eight screwdrivers for slot-head and PHILLIPS® screws

- 324 D/0,4x2,5x50
- 324/0,5x3x75-0,8x4x100-1x5,5x125-1,2x6,5x150
- 324 PH/0x75-1x75-2x100

| n°xa | L mm     | code |  |
|------|----------|------|--|
| 640  | 03240250 | 1    |  |



### 324 SH10

#### Set of ten screwdrivers for slot-head and PHILLIPS® screws

- 324 D/0,4x2,5x50-0,5x3x75-0,6x3,5x100
- 324/0,8x4x100-1x5,5x125-1,2x6,5x150
- 324 PH/0x75-1x75-2x100-3x150

| n°xa | L mm     | code |  |
|------|----------|------|--|
| 890  | 03240255 | 1    |  |




## 324 SH12

### Set of twelve screwdrivers for slot-head, PHILLIPS® and POZIDRIV®-SUPADRIV® screws

- 324 D/0, 4x2, 5x50
- 324/0, 5x3x75-0, 8x4x100-1x5, 5x125-1, 2x6, 5x150
- 324 N/1x5, 5x35
- 324 PH/0x75-1x75-2x100
- 324 NPH/2x35
- 324 PZ/1x75-2x100

| gr  | code     |   |
|-----|----------|---|
| 950 | 03240251 | 1 |



## 324 TX

### Screwdrivers for TORX® screws

- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa    | L mm | code     |   |
|---------|------|----------|---|
| T6x50   | 145  | 03240071 | 5 |
| T7x50   | 145  | 03240072 | 5 |
| T8x50   | 145  | 03240073 | 5 |
| T9x75   | 170  | 03240074 | 5 |
| T10x75  | 179  | 03240075 | 5 |
| T15x75  | 184  | 03240076 | 5 |
| T20x100 | 220  | 03240077 | 5 |
| T25x100 | 220  | 03240078 | 5 |
| T27x100 | 220  | 03240079 | 1 |
| T30x125 | 245  | 03240080 | 1 |
| T40x150 | 275  | 03240081 | 1 |



## 324 TX/S7

### Set of seven screwdrivers for TORX® screws

- 324 TX T10x75-T15x75-T20x100-T25x100-T27x100-T30x125-T40x150

| gr  | code     |   |
|-----|----------|---|
| 810 | 03240264 | 1 |




## 324 TX/S11

### Set of eleven screwdrivers for TORX® screws

- 324 TX T6x50-T7x50-T8x50-T9x50-T10x75-T15x75-T20x100-T25x100-T27x100-T30x125-T40x150

| gr  | code     |   |
|-----|----------|---|
| 920 | 03240266 | 1 |



## 324 STX

### Screwdrivers for TORX® Tamper Resistant® screws

- For safety screws
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa    | L mm | code     |   |
|---------|------|----------|---|
| T10x75  | 179  | 03240086 | 5 |
| T15x75  | 184  | 03240087 | 5 |
| T20x100 | 220  | 03240088 | 5 |
| T25x100 | 220  | 03240089 | 5 |
| T27x100 | 220  | 03240090 | 1 |
| T30x125 | 245  | 03240091 | 1 |
| T40x150 | 275  | 03240092 | 1 |




## 324 STX/S7

### Set of seven screwdrivers for TORX® Tamper Resistant® screws

- 324 STX T10x75-T15x75-T20x100-T25x100-T27x100-T30x125-T40x150

| gr  | code     |   |
|-----|----------|---|
| 810 | 03240093 | 1 |




## 324 H

### Screwdrivers for slot-head screws

- Model with hexagonal drive and hexagonal blade for powerful tightening, also with a wrench
- Metal rear dome to protect the beating zone
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| axbxc mm    | L mm | mm | code     |   |
|-------------|------|----|----------|---|
| 0,8x4x100   | 204  |    | 03240133 | 1 |
| 1x5,5x125   | 234  | 8  | 03240134 | 1 |
| 1,2x6,5x150 | 270  | 10 | 03240135 | 1 |
| 1,2x8x175   | 300  | 11 | 03240136 | 1 |
| 1,6x10x175  | 300  | 12 | 03240137 | 1 |
| 2x12x200    | 300  | 14 | 03240138 | 1 |
| 2,5x14x250  | 375  | 14 | 03240139 | 1 |



## 324 HPH

### Screwdrivers for Phillips screws

- Model with hexagonal drive and hexagonal blade for powerful tightening, also with a wrench
- Metal rear dome to protect the beating zone
- Ergonomic three-material grip
- Special Silicon Chrome Manganese steel blade
- Chrome plated finish with burnished tip

| n°xa  | L mm | mm | code     |   |
|-------|------|----|----------|---|
| 1x100 | 209  | 8  | 03240141 | 1 |
| 2x125 | 245  | 10 | 03240142 | 1 |
| 3x150 | 275  | 12 | 03240143 | 1 |