




PRODUCT NUMBER
58335-YYY(LF)



NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING: SEE DRAWING C-8626-000P
SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
ERICSSON PART NUMBER & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8626-000P

TIN LEAD PART NUMBER:
58335-YYY

LEAD FREE PART NUMBER:
58335-YYLFF

YY DEFINITION: SEE SHEET 3

PLATING IN CONTACT AREA	
DASH NUMBER	PERFORMANCE LEVEL
3YY or 3YYLF	IEC CLASS I
7YY or 7YYLF	ERICSSON SPECIAL


rev	ecn no	dr	date
A	VI2084	TAB	2001/08/30
B	LS2012	SPE	2002/03/13
C	LS05-0065	JTA	2005/08/02
D	LS06-0084	LGO	2006/06/30
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	S.PERRICHOT	2002/03/13	ANGULAR	LINEAR	0. X ±0.3		size A4	Scale 1:1		
Eng	PH.LEGARE	2002/03/13			0. XX ±0.1					
Chr	PH.LEGARE	2002/03/13			0° ±2° 0. XXX ±0.05					
Appr	PH.LEGARE	2002/03/13			Product family					
					METRAL		Spec ref			
			title METRAL SIGNAL HEADER			dwg no 58335C			Rev. D	
			ERICSSON, 5 ROW PRESS-FIT							
			catalog no			CUSTOMER COPY			sheet 1 of 3	

REV F - 2006-04-17



Copyright FCI.



KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30

REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION



Copyright FCI.

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS		OTHERWISE SPECIFIED						
Dr	S.PERRICHOT	2002/03/13	ANGULAR	LINEAR	0.X		±0.3	size A4	Scale 2:1		
Eng	PH.LEGARE	2002/03/13			0.XX		±0.1				
Chr	PH.LEGARE	2002/03/13	0°	±2°	0.XXX		±0.05	ECN			
Appr	PH.LEGARE	2002/03/13	Product family				METRAL		Spec ref		
			Title METRAL SIGNAL HEADER ERICSSON, 5 ROW PRESS-FIT				dwg no 58335C		Rev D		
catalog no											
							CUSTOMER COPY		sheet 2 of 3		

REV F - 2000-04-17



Copyright FCI.

REV F - 2009-04-17

METRAL P/N	ERICSSON P/N	DIM C	DIM D	CONTACT CODE MOD. I					
				ROW	1	2	3	4	5 6
58335-X01	RPV 623 1123	11.93	10.00	E	2	2	2	2	2 2
				D	2	2	2	2	2 2
				C	2	2	2	2	2 2
				B	2	2	2	2	2 2
				A	2	2	2	2	2 2

METRAL P/N	ERICSSON P/N	DIM C	DIM D	CONTACT CODE MOD. I					
				ROW	1	2	3	4	5 6
58335-X02	RPV 623 1124	11.93	10.00	E	3	3	3	3	3 3
				D	3	3	3	3	3 3
				C	2	2	2	2	2 2
				B	3	3	3	3	3 3
				A	3	3	3	3	3 3

METRAL P/N	ERICSSON P/N	DIM C	DIM D	CONTACT CODE MOD. I					
				ROW	1	2	3	4	5 6
58335-X03	RPV 623 1125	11.93	10.00	E	4	4	4	4	4 4
				D	4	4	4	4	4 4
				C	4	4	4	4	4 4
				B	4	4	4	4	4 4
				A	4	4	4	4	4 4

METRAL P/N	ERICSSON P/N	DIM C	DIM D	CONTACT CODE MOD. I					
				ROW	1	2	3	4	5 6
58335-X04	to be added later	11.93	10.00	E	1	1	1	1	1 1
				D	2	2	2	2	2 2
				C	3	3	3	3	3 3
				B	2	2	2	2	2 2
				A	1	1	1	1	1 1

www.fciconnect.com			surface ISO 1302 ☒		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	S.PERRICHOT	2002/03/13	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1:1			
Eng	PH.LEGARE	2002/03/13			0.XX	±0.1					
Chr	PH.LEGARE	2002/03/13	0° ±2°		0.XXX	±0.05	ECN				
Appr	PH.LEGARE	2002/03/13	Product family				METRAL		Spec ref		
			Title METRAL SIGNAL HEADER				dwg no 58335C			Rev. D	
			ERICSSON, 5 ROW PRESS-FIT								
			catalog no				CUSTOMER COPY			sheet 3 of 3	