

## Honeywell Sensing and Control

Search


[narrow your search](#)

### Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9736)

### Technology

- Control and Instrumentation (1063)
- Electromechanical (9297)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

### 192-503QET-A01 Discrete Thermistors

(Home : Products)



Actual product appearance may vary.

192 Series, Uni-Curve with bare leads and epoxy, 50,000 Ohm resistance,  $\pm 0,2$  °C [0.36 °F] tolerance, 25/85 BETA = 4261

[Sales & Service](#)
[Distributor Inventory](#)

### Need Help?

[Click here to contact us](#)
[Overview](#)[Specs](#)[Documentation](#)[Application Notes](#)

### Product Specifications

|                       |                                     |
|-----------------------|-------------------------------------|
| Availability          | Global                              |
| Resistance            | 50,000 Ohm                          |
| Tolerance             | $\pm 0,2$ °C [0.36 °F]              |
| Accuracy              | 0 °C to 70 °C [32 °F to 158 °F]     |
| Beta                  | 4261                                |
| Operating Temperature | -60 °C to 150 °C [-76 °F to 302 °F] |
| Diameter              | 2,413 mm [0.095 in]                 |
| Termination Material  | 32 Gauge tinned copper, alloy 180   |
| Lead Length           | 38,1 mm [1.50 in]                   |
| Time Constant in Air  | 15.0 s                              |
| Dissipation Constant  | 0,75 m/W°C                          |
| Series Name           | 192                                 |