

**A****Pushbutton**

PHB Series Short Stroke Pushbutton Switches

NEW!

Features/Benefits

- Momentary or latching action
- Low cost, reliable contact design
- 2 & 4 pole configurations
- Sealed contacts
- Optional buttons
- RoHS compliant

Typical Applications

- Computers and peripherals
- Instrumentation and measurement equipment
- Non-power, on-off switch applications

Specifications

RATING: 1 A @ 15 V DC

DIELECTRIC STRENGTH (50 Hz/1 min.): 500 V DC between terminals or between terminals and frame for 1 minute

OPERATING LIFE: 10,000 cycles at rated load

CONTACT RESISTANCE: 20 m Ω ohms initial

INSULATION RESISTANCE: 100 M Ω ohms

TOTAL TRAVEL/LATCHING TRAVEL: 2.5mm ($\pm$ 0.5 mm) /
1.5mm ($\pm$ 0.5 mm) to latch EE option (push-push)

OPERATING FORCE:

2U option: 170 grams $\pm$ 100 grams (1.67 $\pm$ 0.98N)

4U option: 230 grams $\pm$ 100 grams (2.26 $\pm$ 0.98N)

OPERATING TEMPERATURE: -10°C to 60°C

BOUNCE TIME: $\leq$ 10 ms

SEALING: Sealed contacts.

PACKAGING: Switches; Tray pack - 100 switches per tray;
Optional Caps; Bulk bag - 100 caps per bag

Materials

FIXED TERMINAL: Brass, silver plated

MOVABLE CONTACT: Phosphor bronze, silver plated

COVER: PA 66 Black

COVER TO BASE RETAINING CLIP: POM

ACTUATOR: POM

RETURN SPRING: Stainless steel

SPRING RETAINING RING: Steel, nickel plate


BASE: Phenolic resin

TERMINAL SEAL: Epoxy.

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. For additional options not shown in catalog, consult Customer Service Center.



Caps (order separately)



INDEXED	COLOR
G001A	BLACK
G001G	GRAY
G001I	IVORY
G001R	RED

RECTANGULAR	COLOR
G002A	BLACK
G002G	GRAY
G002I	IVORY
G002R	RED

ROUND	COLOR
G003A	BLACK
G003G	GRAY
G003I	IVORY
G003R	RED

SQUARE	COLOR
G004A	BLACK
G004G	GRAY
G004I	IVORY
G004R	RED

C&K

Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

NEW!

PHB Series Short Stroke Pushbutton Switches




A


Pushbutton

TERMINATION



TS STRAIGHT



SN KINKED (PLUG IN)



POLES	MODEL NO.	DIM 'A'	ACTION
4	PHB4UEE1A	22,5	PUSH/PUSH
	PHB4U0A1A	22,5	MOMENTARY
2	PHB2UEE1A	15,0	PUSH/PUSH
	PHB2U0A1A	15,0	MOMENTARY



Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

www.ck-components.com



PHB Series Short Stroke Pushbutton Switches

NEW!


CAPS

A

Pushbutton


Indexed

- G001A Black
- G001G Gray
- G001I Ivory
- G001R Red




Rectangular

- G002A Black
- G002G Gray
- G002I Ivory
- G002R Red





Round

- G003A Black
- G003G Gray
- G003I Ivory
- G003R Red



Square

- G004A Black
- G004G Gray
- G004I Ivory
- G004R Red



C&K



Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change