

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


F

REVISED & REDRAWN PER 0720-0921-96

10MAY96

DKS

DMS



- 1 MATERIAL THK: 1.02 ± 0.08 [0.040 ± 0.003]
2 WIRE INSULATION DIA: 7.57 [0.298] MAX
3 TAPE MOUNTED PER 115-11001

BODY: COPPER PER ASTM B-152
TIN PL 0.00254 [0.00100] MIN THK
PER MIL-T-10727

INSULATION: PVC COLOR: RED
METALLIC SLEEVE: COPPER PER ASTM B-152
METALLIC BAND: STEEL PER ASTM A-109

~~2-322048-2~~
OBSOLETE

322048

MATERIAL & FINISH

AMP
PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT
INFORMATION OR COPIES
OF DRAWINGS AND
TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

RECOMMENDED OPERATING TEMPERATURE:
105°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
-
SOLID OR STRANDED

FOR APPLICATION
TOOLING INFORMATION


TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]



MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [0.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH

SEE TABLE

DWN

DK SCHRUM

10MAY96

CHK

DM SWARTZ

13MAY96

APVD

JL MECKLEY

13MAY96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE,
AMPLI-BOND™,
WIRE SIZE: 8 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-322048

SCALE
4:1SHEET
1 OF 1REV
F