

SEALED LEAD-ACID BATTERIES (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7

Part No.	Figure No.	Nominal Voltage (V)	Amp Hours	Dimensions								Weight per Piece		Carton Quantity	Terminal Type
				Length		Width		Height		Total Height					
				in	mm	in	mm	in	mm	in	mm	lbs	kgs		
GC1.2-6F1	1	6	1.2	3.82	97.03	.94	23.88	2.03	51.56	2.26	57.40	0.30	0.66	30	F1
GC7-6F1	3	6	7.0	5.94	150.88	1.34	34.04	3.70	93.98	3.94	100.08	1.34	2.94	8	F1
GC200-6B	N/A	6	210.0	12.05	306.07	6.61	167.89	8.62	218.95	8.86	225.04	33.00	72.60	1	B
GC3.2-8F1	2	8	3.2	5.28	134.11	1.44	36.58	2.48	62.99	2.72	69.09	0.96	2.11	10	F1
GC0.8-12WL	N/A	12	.8	3.78	96.1	.98	24.89	2.44	61.98	2.44	61.98	.37	.80	20	WL
GC2.3-12F1	4	12	2.5	7.01	178.05	1.38	35.05	2.36	59.94	2.60	66.04	1.03	2.27	20	F1
GC4-12F1	5	12	4.0	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC4.5-12F1	5	12	4.6	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC5-12F1	5	12	5.4	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC7-12F1	7	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F1
GC7-12F2	6	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F2
GC7-12F1-FR	7	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F1
GC10-12F2	6	12	10.5	5.94	150.88	3.86	98.04	3.74	95.00	3.98	101.09	3.40	7.48	5	F2
GC12-12F2	6	12	12.0	5.94	150.88	3.86	98.04	3.74	95.00	3.98	101.09	3.90	8.58	4	F2
GC18-12F2	N/A	12	18.0	7.15	181.61	3.03	76.96	6.59	167.39	6.59	167.39	5.70	12.54	2	F2
GC18-12NB	N/A	12	18.0	7.15	181.61	3.03	76.96	6.59	167.39	6.59	167.39	5.70	12.54	2	NB
GC26-12F2	N/A	12	26.0	6.56	166.62	6.89	175.01	4.92	124.97	4.92	124.97	8.80	19.36	1	F2
GC26-12NB	N/A	12	26.0	6.56	166.62	6.89	175.01	4.92	124.97	4.92	124.97	8.80	19.36	1	NB
GC35-12NB	N/A	12	37.0	7.68	195.07	5.12	130.05	6.46	164.08	7.09	180.09	11.70	25.74	1	NB
GC38-12NB	N/A	12	38.0	7.76	197.10	6.50	165.10	6.69	169.93	6.69	169.93	13.60	29.92	1	NB
GC55-12NB	N/A	12	56.0	8.98	228.09	5.43	137.92	8.19	208.03	8.98	228.09	17.70	38.94	1	NB