


Types LC EIA Class 3, Semiconductor Type Reduced Titanite Disc Ceramic Capacitors



EIA Class 3 reduced titanite disc ceramic capacitors are ideal for use in transistorized circuitry for bypass and coupling applications.

Highlights

- High Capacitance
- Low power factor
- Superior radio frequency impedance
- Meets RS-198C for Class 3 ceramic capacitors
- Radial leads

Specifications

Capacitance Range:	.01 to .10 μF
Voltage Range:	25 Vdc
Tolerance:	$\pm 20\%$
Operating Temperature Range:	-30°C to $+85^\circ\text{C}$
Insulation Resistance:	1 megohm minimum
Breakdown Voltage:	2.5 x rated (5 seconds Max.)
Power Factor:	1.5% Max. @ 1 KHz
Lead Length:	1.0 inch minimum

Ratings

Cap (μ F)	Catalog Part Number	Tol. ($\pm$)	Temp. Coef.	Size				Size			
				D	T	S	d	D	T	S	d
25 Vdc											
.010	LC103M*	20%	Y5R**	.235	.138	.250	.025	6.0	3.5	6.4	.6
.100	LC104M*	20%	Y5R**	.495	.138	.250	.025	12.6	3.5	6.4	.6

*available only until stock is depleted

**maximum capacitance change over temperature rating: $\pm 15\%$

Physical Specifications

Case: Conformal Coating

Lead material: Tinned copper wire. (Minimum lead content: 5%)


Tape and Reel Available upon Request

Leads are formed to .200 (5.0mm) lead spacing

For D less than .315 (8.0mm)

- Quantity/Reel = 2500 pcs

Tape and reel not available for greater than .472" (12mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

[L081C561](#) [L061C202](#) [L063C152](#) [L063C181](#) [L063C331](#) [L103C680](#) [L103C683](#) [L105C331/471](#) [L083C271](#)
[L091C222](#) [L091S105](#) [L061C103LF](#) [L061C102LF](#) [L061C104LF](#) [L061C121LF](#) [L061C152LF](#) [L061C153LF](#)
[L061C202LF](#) [L061C221LF](#) [L061C222LF](#) [L061C223LF](#) [L061C271LF](#) [L061C272LF](#) [L061C331LF](#) [L061C332LF](#)
[L061C333LF](#) [L061C471LF](#) [L061C472LF](#) [L061C473LF](#) [L063C101LF](#) [L063C102LF](#) [L063C103LF](#) [L063C104LF](#)
[L063C121LF](#) [L063C153LF](#) [L063C181LF](#) [L063C203LF](#) [L063C222LF](#) [L063C223LF](#) [L063C224LF](#) [L063C271LF](#)
[L063C331LF](#) [L063C332LF](#) [L063C333LF](#) [L063C390LF](#) [L063C392LF](#) [L063C393LF](#) [L063C472LF](#) [L063C473LF](#)
[L063C822LF](#) [L065C221/331LF](#) [L081C101LF](#) [L081C104LF](#) [L081C105LF](#) [L081C123LF](#) [L101C101LF](#) [L101C102LF](#)
[L101C104LF](#) [L101C105LF](#) [L101C121LF](#) [L101C151LF](#) [L101C152LF](#) [L101C153LF](#) [L101C182LF](#) [L101C183LF](#)
[L101C202LF](#) [L101C203LF](#) [L101C221LF](#) [L101C222LF](#) [L101C224LF](#) [L101C271LF](#) [L101C272LF](#) [L101C273LF](#)
[L101C331LF](#) [L101C333LF](#) [L101C391LF](#) [L101C392LF](#) [L101C471LF](#) [L101C473LF](#) [L101C474LF](#) [L101C560LF](#)
[L101C561LF](#) [L101C562LF](#) [L101C681LF](#) [L101C682LF](#) [L101C821LF](#) [L103C101LF](#) [L103C102LF](#) [L103C103LF](#)
[L103C104LF](#) [L103C105LF](#) [L103C121LF](#) [L103C122LF](#) [L103C123LF](#) [L103C151LF](#) [L103C152LF](#) [L103C203LF](#)
[L103C221LF](#) [L103C222LF](#) [L103C223LF](#)