

SURGE SUPPRESSOR, VARISTOR,
AC 24...48V, DC 24...70V,
FOR MOTOR CONTACTORS SZ S0,

General technical data:

Product brand name		SIRIUS
Product designation		surge suppressor
Size of the contactor		S0
Design of the surge suppressor		with varistor
Ambient temperature		
• during storage	°C	-40 ... 80
• during the operating phase	°C	-25 ... 60

Control circuit:




Type of voltage / of the controlled supply voltage		AC/DC
control supply voltage frequency		
• 1 / rated value	Hz	50
• 2 / rated value	Hz	60
Control supply voltage / 1		
• for DC		
• initial rated value	V	24
• final rated value	V	70
• at 50 Hz / for AC		
• initial rated value	V	24
• final rated value	V	48
• at 60 Hz / for AC		
• final rated value	V	48
• initial rated value	V	24

Installation/mounting/dimensions:

built in orientation		any
Type of fixing/fixation		clip-on
Width	mm	30
Height	mm	19
Depth	mm	12

Certificates/approvals:

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)<http://www.siemens.com/industrial-controls/catalogs>**Global Industry Mall (Online ordering system)**<http://www.siemens.com/industrial-controls/mall>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3RT2926-1BB00/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RT2926-1BB00

last change:

Apr 26, 2010