

**Olympic Wire and Cable**

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

**Olympic P/N 366, UL LISTED UL1015, UL1032, UL1230****UL LISTED UL1015, UL1032, UL1230**

Stranded Tinned Copper, Color Coded PVC Insulation.

**Characteristics:**

Temperature Rating — 40°C to +105°C

Resistant to acids, alkalis, oil, flame, moisture and fungus

**SPECIFICATIONS**

|                       |                                                                                                        |
|-----------------------|--------------------------------------------------------------------------------------------------------|
| Conductor Size        | 12 AWG                                                                                                 |
| Stranding             | 65/30 Tinned Copper                                                                                    |
| Insulation            | PVC                                                                                                    |
| Nom. Wall Thickness   | 0.031 in                                                                                               |
| Nom. O.D.             | 0.158 in                                                                                               |
| UL Style              | 1015<br>1032<br>1230<br>MTW                                                                            |
| UL Rating             | 600 V, 90°C, 1000 V                                                                                    |
| UL Flame Test         | VW-1                                                                                                   |
| CSA Type              | TEW                                                                                                    |
| CSA Flame Test        | FT-1                                                                                                   |
| Boat Cable            | BC-5W2                                                                                                 |
| Operating Temperature | -40 to +105 °C                                                                                         |
| RoHS Compliant        | <br>RoHS Compliant |
| Color Code            | Hook Up Wire Color Code Chart                                                                          |