

531-315.

Type	Side Walls	Pg Knockouts	Inside Height	Ref. No.	Unit
POLYSTYRENE - COVER GREY RAL 7035					
PS 1818- 9	with Pg		75 mm	115-407	8/2
PS 1818-11	with Pg		97 mm	115-907	8/2
PS 1818-16	with Pg		150 mm	114-407	4/1
PS 1818-21	with Pg		200 mm	114-907	4/1
PS 1818- 9-o	smooth		75 mm	110-407	8/2
PS 1818-11-o	smooth		97 mm	110-907	8/2
PS 1818-16-o	smooth		150 mm	109-407	4/1
PS 1818-21-o	smooth		200 mm	109-907	4/1
POLYSTYRENE - COVER TRANSPARENT					
PS 1818- 9-t	with Pg		75 mm	116-007	8/2
PS 1818-11-t	with Pg		97 mm	116-507	8/2
PS 1818-16-t	with Pg		150 mm	117-007	4/1
PS 1818-21-t	with Pg		200 mm	117-507	4/1
PS 1818- 9-to	smooth		75 mm	111-007	8/2
PS 1818-11-to	smooth		97 mm	111-507	8/2
PS 1818-16-to	smooth		150 mm	112-007	4/1
PS 1818-21-to	smooth		200 mm	112-507	4/1
POLYCARBONATE - COVER GREY RAL 7035					
PC 1818- 9	with Pg		75 mm	125-407	8/2
PC 1818-11	with Pg		97 mm	125-907	8/2
PC 1818-16	with Pg		150 mm	126-407	4/1
PC 1818-21	with Pg		200 mm	126-907	4/1
POLYCARBONATE - COVER TRANSPARENT					
PC 1818- 9-t	with Pg		75 mm	135-007	8/2
PC 1818-11-t	with Pg		97 mm	135-507	8/2
PC 1818-16-t	with Pg		150 mm	136-007	4/1
PC 1818-21-t	with Pg		200 mm	136-507	4/1

TK 1818
Empty
Enclosure
182 x 180^{mm}
Type of
Protection
IP 66

Knockouts: = Pg 16/11 = Pg 16 = Pg 21/16 = Pg 29/21					
				Max. number of Pg drill holes per box side	
		Pg	A	B	
		7	21	18	
		9	12	10	
		11	12	10	
		13.5	10	8	
		16	10	8	
		21	4	3	
		29	3	2	
		36	2	2	

All dimensions in millimeters