


Model 3784 Minigrabber® Test Clip To Stacking Miniature Banana Plug



FEATURES:

- Provides a Minigrabber output from a miniature Banana Jack.
- Mates to Model 2142-* or any miniature Banana Jack.
- Miniature Banana plug is vertically stackable.

MATERIALS:

Conn: 1st end - Minigrabber®

Material: Contact - Beryllium Copper

Spring – Stainless steel

Finish: Contact – Gold plated

Insulation: Glass filled nylon. Color matches color of wire.

Marking: “MINIGRABBER® “POMONA ELECTRONICS.”

Wire: 20 AWG, stranding 41 x 36 t.c., PVC insulated, 2.21 (.087) O.D.

Color: See Ordering Information

Marking: “POMONA 3784-*.”

Conn: 2nd end – Miniature Banana Plug

Material: Spring - Beryllium Copper

Plug Body – Brass

Finish: Gold plated over electroless nickel

Insulation: Polypropylene molded to plug body and wire.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max

Operating Voltage: 300 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 3784-XX-*

XX = Cable Lengths, Standard Lengths 24” (610), 36” (914),.

Additional lengths and colors can be quoted upon request.

*= Color, -0 Black, -2 Red,

Ordering Example: 3784-36-2 Indicates 36” in length, color is Red