


REV	ECR NO.	DATE
A	B744	07/08/93
NEW RELEASE		

7 1 3/4 FLASHING LED
NOTE: SEE SPEC. TABLE



HOUSING: BLACK NYLON

WIRE LEADS:
5.94 (150.9) / 6.25 (158.8)
#24 AWG, .015 (1.58) WALL PVC
RED ANODE, BLACK CATHODE
STRIPPED .43 (10.9) / .57 (14.5)



ISOMETRIC VIEW
FOR REF. ONLY

MODEL No.	COLOR	LED No.
5100H1FL	RED	43B0H1
5100H5FL	GREEN	43B0H5
5100H7FL	YELLOW	43B0H7

JUN 01 1993

REV. C

DIMENSIONS ARE IN INCHES (mm).

PART NO.		TITLE	
AS NOTED		5100H FL SERIES (FLASHING LED)	
MATERIAL		INDUSTRIAL DEVICES, INC. HARRISON, NEW JERSEY	
FINISH		DRAWN M. MARQUES CHECKED B. M. 7/8/93 DATE 7/8/93	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE 4 : 1	
FRACTIONS 1/16, 1/8, 3/16, 1/4, 3/8, 1/2, 5/8, 3/4, 7/8, 1, 1 1/4, 1 1/2, 1 3/4, 2, 2 1/4, 2 1/2, 3, 3 1/4, 3 1/2, 4, 4 1/4, 4 1/2, 5, 5 1/4, 5 1/2, 6, 6 1/4, 6 1/2, 6 3/4, 7, 7 1/4, 7 1/2, 8, 8 1/4, 8 1/2, 8 3/4, 9, 9 1/4, 9 1/2, 9 3/4, 10, 10 1/4, 10 1/2, 10 3/4, 11, 11 1/4, 11 1/2, 11 3/4, 12, 12 1/4, 12 1/2, 12 3/4, 13, 13 1/4, 13 1/2, 13 3/4, 14, 14 1/4, 14 1/2, 14 3/4, 15, 15 1/4, 15 1/2, 15 3/4, 16, 16 1/4, 16 1/2, 16 3/4, 17, 17 1/4, 17 1/2, 17 3/4, 18, 18 1/4, 18 1/2, 18 3/4, 19, 19 1/4, 19 1/2, 19 3/4, 20		REV. B11557	
SHEET 1 OF 1		REV. A	



NOTE:
MOUNTING HOLE .249 (6.33) / .254 (6.45) DIA.
IN PANELS .031 (1.58) / .062 (1.58) THICK.

DO NOT SCALE

