

**Wiha Industrial SoftGrip Pliers & Cutters**

Made by Wiha

**Industrial SoftGrip Diagonal Cutters**

[SHOP](#)
**309 | Industrial Diagonal Cutters DIN ISO 5749**

Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edge is achieved with additional induction hardening to approx. 64HRC. Special C70 tool steel forgings hardened and tempered. For soft & medium hard wire.

Item	mm	Inch	Cutting Capacity	Pkg.	lbs.
30923	140	5.5	#6	1	.45
30925	160	6.3	#6	1	.57
30927	180	7.0	#6	1	.69

**Industrial SoftGrip H. Leverage Diag. Cutters**

[SHOP](#)
**309 | Industrial High Leverage Diagonal Cutters DIN ISO 5749**

Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edges are achieved through additional induction hardening to approx. 64HRC. C60 special C70 tool steel hardened and tempered.

Item	mm	Inch	Cutting Capacity	Pkg.	lbs.
30929	160	6.3	#6	1	.57
30931	180	7.0	#5	1	.68
30933	200	8.0	#4	1	.89

**Industrial SoftGrip Heavy Duty End Nippers**


[SHOP](#)
**30939 | Industrial Heavy Duty End Cutting Nippers**

Induction hardened cutting edges. Special tool steel. Two component SoftGrip handle. Gripping and right-angled bending of wires and sheet metal parts. Two component SoftGrip handle.

Item	mm	Inch	Pkg.	lbs.
30939	200	8.0	1	.54

[SHOP](#)
**Industrial SoftGrip Standard Adj. Pliers**


With box joint


  
[SHOP](#)
**30937 | Industrial Adjustable Pliers DIN ISO 8976**

10 opening settings provides optimal adjustment to objects being gripped. Long life achieved through additional induction hardening of jaws to approx. 64HRC. Chrome-vanadium tool steel forgings, hardened and tempered. Two component SoftGrip ergonomic handle. Black finish.

Item	mm	Inch	Capacities	Pkg.	lbs.
30937	250	10.0	1 3/4" 2"	1	.94

**Industrial SoftGrip Push Button Adj. Pliers**


With box joint


  
[SHOP](#)
**30943 | Industrial Slide Lock Adjustable Pliers - Box Joint - With Push Button Setting. DIN ISO 8976**

Extra narrow head for working small spaces. Rapid and simple push button setting and locking. Long life achieved through additional induction hardening of jaws to approx. 64HRC. Finger jam protection for safe operation at all settings. CVM tool steel forgings, hardened and tempered. SoftGrip handles.

Item	mm	Inch	Capacities	Pkg.	lbs.
30943	250	10.0	1 3/4" 2"	1	.95

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wiha](#):

[30937](#) [30943](#) [30923](#) [30927](#) [30939](#) [30925](#) [30933](#) [30929](#) [30926](#) [30928](#) [30931](#)