





DESCRIPTION: 44-PIN MALE / FEMALE HIGH DENSITY GENDER CHANGER

SPECIFICATION:

- INSULATOR: PBT GLASS FIBER REINFORCED UL 94VO
- CONTACT: BRASS
- CONTACT PLATING: GOLD PLATED OVER NICKEL
- SHELL: TIN PLATED SHELL
- CURRENT RATING: 3 AMP
- DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
- INSULATION RESISTANCE: 1,000 MegOHMS MIN @500 VDC
- TEMPERATURE: -55° C - +105° C

NOTE:

- LABEL: YELLOW COLOR WITH BLACK CHARACTORS
- ONE SIDE: MINI GENDER CHANGER
- OTHER SIDE: U.S.A. PATENT 5199906



44-PIN MALE		44-PIN FEMALE
1	---	1
2	---	2
3	---	3
~		
43	---	43
44	---	44
SHELL	---	SHELL
PIN OUT		

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
10-15-07

CHECKED:

DATE:

SCALE:
1.5 : 1

SHEET
1 OF 1

REV
1

DWG NO.
GCHDLP44M44F

RoHS COMPLIANT

NorComp