

250-2600 Watts

HELIOS

Mini FLEX

2600W 48 VDC Compact Flexible Power Solution



Special Features

- Up to 2600 W Power Output and up to 5200 W with optional double shelves
- Front access unit.
- Operable in 110VAC or 220VAC systems
- One to four 250W/500W/650W output rectifiers providing up to 1950W with N+1 redundancy
- Distribution: 8 fuse positions (0 to 10A each)
- Power factor correction
- Current sharing
- Standard Low Voltage Disconnect (LVD) with LVD bypass and LVD test.
- Hot plug-in rectifier modules
- Soft switching technology
- Brackets for 1.5 or 4.75 inch depth installation
- Full complement of LED and output alarms
- Connection for battery string
- Compact dimensions
 - Power shelf: 19"W x 4.94"H x 13.2"D
 - Battery tray: 17.3"W x 7"H x 14.46"D
- CE Marking

Environmental

EMC/EMI: FCC Class B, CISPR Class B for digital devices, Telcordia GR-1089-CORE, Class B, EN 300 386-2

Temperature: -40° to +65°C (+50°C for high altitude)

Humidity: 0 to 95% RF (non-condensing)

Acoustic noise: < 60dB for full system

Cooling: forced air, horizontal (side to side)

Shock and vibration: meets Telcordia GR-63- CORE

Fire resistance: UL 94VO, TR-NWT-000154, Sec 7.2

Voltage surge protection: meets Telcordia GR-1089 section 4.5.9

Electrical Specs

Input

AC input voltage range	110/220VAC (86-264 VAC for 250 W, 176-264 VAC for 500 W, 186-264 VAC for 650W rectifiers)
Frequency	45 – 65 Hz
Efficiency	> 86% at full load
Power factor	0.99 (50 – 100% output load)
Total harmonic distortion	< 6.5% at loads over 50% of rated current

Output

DC output voltage range	-54.5 VDC $\pm$ 0.27 VDC (Factory preset)
Output Current	18.35A (1000W), 36.70A (2000W), 47.71 A (2600W) @ -54.5 VDC
Maximum output power	1120 W, 2240 W, 2730 W @ power limit. Different preset voltages avail.
Voltage regulation	$\pm$ 0.5% load/line and $\pm$ 1.0% load/line°C
Dynamic response	$\pm$ 5% for 10% to 90% or 90% to 10% load step changes
Capacitor precharge	automatic upon insertion
Voice frequency noise	<55dB rnc @ 10% load
High frequency noise	<250 mV p-p

Battery Tray - A0802970

(for 1000 W application only)

Protection disconnect device	Built in 30 A circuit breaker
Batteries	Designed to accommodate 30 A/h M12V30 Marathon VRLA batteries

Safety

Rectifier:	UL1950
Power Shelf:	UL1801, CSA 22.2#950, IEC-950, VDE

AMERICAS

5810 Van Allen Way
Carlsbad, CA 92008
Telephone: 760-930-4600
Facsimile: 760-930-0698

EUROPE

Astec House, Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX, UK
Telephone: 44 (1384) 842-211
Facsimile: 44 (1384) 843-355

ASIA

Units 2111-2116, Level 21
Tower1, Metroplaza
223, Hing Fong Road
Fwai Fong, New Territories
Hong Kong
Telephone: 852-2437-9662
Facsimile: 852-2402-4426



Ordering Information

HMFLEX- - 		Multiplier			
		1	2	3	4
Rectifier Base	1	250W	500W	750W	1000W
	2	500W	1000W	1500W	2000W
	3	650W	1300W	1950W	2600W

EXAMPLE: HMFLEX- 1 - 3

750 W total power
with three 250 W rectifiers

Helios MiniFLEX includes Power Shelf, LVD, and distribution; eight 10A GMT fuses

Options:

- P0917017 Helios MiniFlex 23" adapter bracket kit
- A080297 Battery Shelf and battery tray cable assembly to accommodate 30 A hr battery string for HMFLEX-1- system (battery not included)
- P0917018 Battery shelf 23" adapter bracket kit
- P0944645 60" power cord for up to 220 VAC with Hubbel #2321AC plug
- P0944646 120" power cord for up to 220 VAC with Hubbel #2321AC plug
- P0944647 180" power cord for up to 220 VAC with Hubbel #2321AC plug
- P0944716 60" power cord for up to 220VAC without AC plug
- P0944718 120" power cord for up to 220VAC without AC plug
- P0944719 180" power cord for up to 220VAC without AC plug

