


PROD	LOC	DIST	REVISIONS						
4086	DF	SO	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
CODE						K	REV & REDRAWN; 0600-5719-96 CT	9-96	SG

PART NO.	DIM A	
862550-1	6.00	[152.4]
862550-2	8.00	[203.2]
862550-3	10.00	[254.0]
862550-4	12.00	[304.8]
862550-5	15.00	[381.0]
862550-6	18.00	[457.2]
862550-7	21.00	[533.4]
862550-8	24.00	[609.6]
862550-9	36.00	[914.4]
1-862550-0	30.00	[762.0]
1-862550-1	110.00	[2794.0]
1-862550-2	72.00	[1828.8]
1-862550-3	48.00	[1219.2]
1-862550-4	7.00	[177.8]
1-862550-5	5.00	[127.0]
1-862550-6	60.00	[1524.0]



- 1

TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.1]
24 INCHES [609.6] & UP = ±1%
- 2

MARKED PER MIL-STD-130 LOCATED APPROX IN CENTER OF LEAD.
3.

TO MATE WITH AMP LGH-1
RECEPTACLE WITH .88 [22.4] BARREL DEPTH.
4.

OPERATING VOLTAGE: 20 KVDC AT 0 TO 70,000
FEET; -55°C TO 125°C.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± .02 [0.5] 3 PLC DEC ± - ANGLES ± -	DR 9-27-96 C.C.THOMAS		AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 10-30-96 S.GLATFELTER				
	APPD 10-30-96 S.GLATFELTER		NAME		
MATERIAL SEE CALLOUTS	RLSE 10-30-96 C.THOMAS		LEAD ASS'Y, DBL. END, POS. STOP, LGH-1		
	PRODUCT SPEC -				
FINISH SEE CALLOUTS	APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO 862550
	WEIGHT -		SCALE 2:1		SHEET 1 OF 1