

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300480070

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (90°) to Pigtail, 22 AWG PUR Cable, 1.0m (3.28') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E200650

General

Product Family

Industrial Cordsets

Series

130048

Connector End A

Micro-Change (M12)

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Industrial Ethernet Solutions

Performance Category

5e

Product Name

Micro-Change (M12)

Protocol

N/A

Region

America, Asia, Europe

Type

Single Ended

UPC

78678804016

Physical

Cable Diameter

5.59mm (.220")

Cable Length

1.0m (3.28')

Color - Cable Jacket

Teal

Coupling Style

Threaded

Gender

Male-Pigtail

Keyway

D-coded

LED Indicator

No

Material - Cable Jacket

PUR

Material - Connector Body

PUR

Material - Coupling Nut

Nickel-plated Brass

Material - Plating Mating

Gold over Palladium Nickel

Orientation

90° to Pigtail

Poles

4

Temperature Range - Operating

-20°C to +75°C

Wire Size AWG

24

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

1.5A

Voltage - Maximum

30V

Material Info

Engineering Number

E10A00710M010

Reference - Drawing Numbers

Sales Drawing

SD-120108-017



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130048 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION