

Terminal boxes KL with gland plate – KL 1533.510



Product description

Material:	- Enclosure: Sheet steel - Cover: Sheet steel, all-round foamed-in PU seal
Surface finish:	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
Supply includes:	- Enclosure with cover - Quick-release fastener including plastic bushes - Sheet steel gland plates with seals and assembly parts
Packs of:	1 pc(s).
EAN:	4028177251397
Customs tariff number:	94032080

Product features

Dimensions:

- Width: 500 mm
- Height: 200 mm
- Depth: 120 mm

Gland plates:

- Size/Qty. (top/bottom): 2 / 2 + 2

Weight:

- 4.9 kg

Approvals

Approvals:

-  [Bureau Veritas \(EN\)](#)
-  [VDE \(EN, DE\)](#)
-  [UL \(EN\)](#)
-  [TÜV \(EN\)](#)
-  [TÜV \(DE\)](#)
-  [Russian Maritime Register of Shipping \(RU, EN\)](#)
-  [Lloyds Register of Shipping \(EN\)](#)
-  [C-UL \(EN\)](#)
-  [CSA \(EN\)](#)
-  [Germanischer Lloyd \(EN\)](#)

Declarations:

-  [Manufacturer's declaration \(EN, DE\)](#)
-  [Declaration of conformity \(EN, DE\)](#)

Downloads

Documentation:

-  [Instructions \(EN, DE\)](#)

CAD drawings:

- Request