

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.




Jameco Part Number 837118

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				DATE	APPD
				ZONE	LTR	DESCRIPTION			
AF	50				K	REV PER 0G1A-0148-99		4JUN99	JR/JH



- 1 MATES WITH .020±.001×.187 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .060-.135 DIA
- 4 DIMENSION DOES NOT INCLUDE TRIM BURR
- 5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



HOUSING: NYLON, COLOR-RED TRANSLUCENT RECEPTACLE: #3 HARD BRASS TIN PL .000080 MIN THK				2-520409-2		
MATERIAL & FINISH				PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± - MATERIAL SEE TABLE	DR	10/31/88 P FORTNEY		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK	11/2/88 MS FEHER				
	APPD	11/2/88 K RANDOLPH		NAME RECEPTACLE ASSY, ULTRA-FAST PLUS, LOOSE PIECE, .187 SERIES, 22-18 AWG		
	APPD	11/14/88 TL SHUTTER				
	PRODUCT SPEC	108-2044				
FINISH SEE TABLE	APPLICATION SPEC	114-2123		SIZE	FSCM NO	DRAWING NO
	WEIGHT	-		B	00779	520409
				SCALE	4 : 1	SHEET 1 OF 1