



Plastic Boxes - NEMA 4x  
Accessories

## Cable glands



### ***Design Features***

Required to maintain NEMA 4X rating when cables enter or exit a NEMA 1, 2, 4, 4x, 12 or 13 type enclosure. Assembly consisting of black molded nylon body, hex nut, and cable nut and with a rubber gasket and cable seal. Nylon material has UL94V-2 flammability rating and -40C to 100C suggested service temperature.


| Cable Glands   |               |                        |             |
|----------------|---------------|------------------------|-------------|
| Catalog Number | Mounting Size | Mounting Hole Diameter | Cable Range |
| NG-9511        | PG-7          | .50"                   | .12"-.26"   |
| NG-9512        | PG-9          | .61"                   | .16"-.31"   |
| NG-9513        | PG-11         | .73"                   | .20"-.39"   |
| NG-9514        | PG-13.5       | .81"                   | .24"-.47"   |
| NG-9515        | PG-16         | .89"                   | .39"-.55"   |
| NG-9516        | PG-21         | 1.12"                  | .51"-.71"   |
| NG-9517        | PG-29         | 1.47"                  | .71"-.98'   |

PART  
NAME

NEMA 4X GLAND

PART  
No.

NG-9511 TO NG-9517



MATERIAL: NYLON -66, UL-94V2 (NUT, BODY & CABLE NUT)  
 NBR (N) RUBBER (GASKET & CABLE SEAL)  
COLOR: BLACK

| PART NO. | MOUNT<br>THREAD | CABLE RANGE<br>(DIA.) | A     | B     | C     | D     | E     | F     | G     | H     |
|----------|-----------------|-----------------------|-------|-------|-------|-------|-------|-------|-------|-------|
| NG-9511  | PG-7            | 0.118 - 0.256         | 0.197 | 0.315 | 0.488 | 0.307 | 1.102 | 0.039 | 0.827 | 0.201 |
| NG-9512  | PG-9            | 0.158 - 0.315         | 0.283 | 0.374 | 0.563 | 0.307 | 1.169 | 0.056 | 0.921 | 0.201 |
| NG-9513  | PG-11           | 0.197 - 0.394         | 0.374 | 0.512 | 0.717 | 0.307 | 1.236 | 0.058 | 1.047 | 0.201 |
| NG-9514  | PG-13.5         | 0.236 - 0.472         | 0.453 | 0.591 | 0.787 | 0.346 | 1.315 | 0.062 | 1.161 | 0.240 |
| NG-9515  | PG-16           | 0.394 - 0.551         | 0.524 | 0.669 | 0.878 | 0.386 | 1.425 | 0.062 | 1.303 | 0.240 |
| NG-9516  | PG-21           | 0.512 - 0.709         | 0.681 | 0.866 | 1.102 | 0.425 | 1.583 | 0.062 | 1.539 | 0.280 |
| NG-9517  | PG-29           | 0.709 - 0.984         | 0.957 | 1.181 | 1.449 | 0.425 | 1.772 | 0.062 | 1.972 | 0.319 |

PART  
NAME

ADAPTER BRACKET

PART  
No.

AB-2375

MATERIAL: 16 GA. STEEL  
COLOR: BLACK

