



FK21M

Tapered chisel tip penetration probe



Copyright © 2007 Test Products International, Inc.

Application

General purpose light duty penetration applications requiring fast response

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

21

Dimensions

Stem Length: 4.75" (101.6mm)
Diameter: 0.13"/.06"
(3.2/1.6mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane