




## Electrical Specifications:

- Impedance primary: 600Ω  
Secondary: 600Ω load (±1%)
- Impedance variation: +/-10% 1KHz 0.25V series test
- DC resistance primary: 32Ω +/- 10%  
Secondary: 40Ω +/- 10%
- Insertion loss: 1.5 dB max. at 1000Hz
- Frequency response: ±0.5 dB @ 300-3500Hz; 1KHz 0 dB
- Turns ratio: 1:1, +/-3%
- Breakdown voltage: 1500VAC 60Hz HIPOT for 1 minute
- Insulation resistance: @500VDC > 100MΩ

Your source for quality electronics. Toll-free full service  
**(800) 346-6873**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

420-8801