




COIL: @ +25 °C

RESISTANCE 160 OHMS ± 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 6.4 VDC

MUST RELEASE 0.7 VDC

#### ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 100 g's 6 ± 1 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX

RELEASE 4 MS MAX

CONTACT STABILIZATION 2.5 MS MAX

#### CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 6/2/93 CK 6/2/93

**COMMUNICATIONS**  
**INSTRUMENTS, INC.**

CUST. OPL  
CUST. NO. M39016/6-116P

TYPE "HFW" RELAY

HFW1201G01P