

Distributed by:


JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.


Jameco Part Number 154879

Date	Rev.	Description



Model No: A5

TOLERANCE
XX. ± 0.5
X. ± 0.2
.X ± 0.2
.XX ± 0.2




SPECIFICATIONS:

CONTACT RATING : 3 AMPS @ 120 V AC or 28 VDC.
 1 APMS @250 V AC or 0.4VA AMPS @20 V AC or DC
 ELECTRICAL LIFE : 50,000 make-and-break cycles at full load.
 CONTACT RESISTANCE : 10 m Ω max. initial @ 2-4 VDC.
 100 mA, for both coin silver and gold plated contacts.
 INSULATION RESISTANCE : 1,000 M Ω min.
 DIELECTRIC STRENGTH : 1,000 V RMS @ sea level.
 OPERATING TEMPERATURE : -30 $^{\circ}$ C to 130 $^{\circ}$ C

MATERIALS:

CASE : Diallyl phthalate (DAP)(UL-94V-0).
 PLUNGER : Polybutylene terephthalate (PBT) (UL 94V-0)
 BUSHING : Brass, nickel plated.
 HOUSING : Stainless steel.
 TERMINAL/CONTACT : Brass, with silver or gold plated.
 or gold over silver
 SWITCH SUPPORT : Brass, tin plated.



DCC. NO.
A4 DRAWING NO.

MATERIAL	GOLDSUN ELECTRONICS CO., LTD.			
	JAMECO NO.	GOLDSUN NO.		
	154879			
DRAWN: Kiki Chen	Description	PUSHBUTTON SWITCH		Rev. 1
VERIFY PEOPLE: Ada Zheng , Ivy Lan	UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: