


General Specifications

Motor Protection: Auto Restart
Insulation Resistance: 10M Ohm or over with a DC500V
Megger
Dielectric Withstand Voltage: AC 700V 1st
Allowable Ambient Temperature Range:
-10 degree C ~ +70 degree C (Operating)
-40 degree C ~ +70 degree C (Storage)
(non-condensing environment)

**order part 4710KL-05W-B10-E00 Ball
Bearing Fan DC Fans**




4710KL panel cut out




Material

Casing: Plastic (Black) UL94V-0
Impeller: Plastic (Black) UL94V-0
Lead Wire: UL10368, AWG26, +Red, -Black

4710KL characteristic curve



4710KL product drawing



Detailed Specifications

Expected Life:	40 degree C 50,000 Hours (L10)
DC Fan:	Ball Bearing Fan
Nominal Voltage:	24[V]
Operating Voltage Lower:	10[V]
Operating Voltage Upper:	27.6[V]
Current:	0.08[A]
Input Power:	1.92[W]
Speed:	1600[min^{-1}]
Max. Air Flow:	1.8[m^3/min]
Max. Air Flow:	63.5[CFM]
Max. Static Pressure:	17.9[Pa]
Max. Static Pressure:	0.07[In H ₂ O]
Noise:	27[dB]
Mass:	180[g]
Fan Size:	119[mm]
Fan Width:	25[mm]