



Ring Tongues – Nylon Insulated Brazed Seam 8 AWG




Product Number†	UPC (054007-)	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter	Terminals per: Carton Case
MN8-10R/SK	08267	8	10	0.47	0.40	1.26	1.03	0.050	0.31	0.175	0.340	— 200
MN8-14R/SX	15652	8	1/4	0.47	0.40	1.26	1.03	0.050	0.31	0.175	0.340	25 250
MN8-14R/SK	08268	8	1/4	0.47	0.40	1.26	1.03	0.050	0.31	0.175	0.340	— 200
MN8-516RK	08269	8	5/16	0.59	0.45	1.38	1.08	0.050	0.31	0.175	0.340	— 200
MN8-38RK	08270	8	3/8	0.59	0.45	1.38	1.08	0.050	0.31	0.175	0.340	— 200
MN8-12R/SK	08271	8	1/2	0.81	0.69	1.72	1.32	0.050	0.31	0.175	0.340	— 200




MN8-10R/S
Stud Size 10
Wire Range 8




MN8-14R/S
Stud Size 1/4
Wire Range 8



MN8-516R
Stud Size 5/16
Wire Range 8



MN8-38R
Stud Size 3/8
Wire Range 8



MN8-12R/S
Stud Size 1/2
Wire Range 8