






DESCRIPTION: R/A .318" FILTERED D-SUB



	A	B	C	D
9	1.204 30.6	.984 25.0	.480 12.20	.433 10.99
15	1.535 39.0	1.312 33.3	.480 12.20	.757 19.23
25	2.078 52.8	1.850 47.0	.480 12.20	1.305 33.15
37	2.724 69.2	2.500 63.5	.480 12.20	1.957 49.71



479-YYY-112RYY1

SERIES _____
POSITIONS _____
009
015
025
037
050
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
1 - DIP SOLDER
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
58 = STABILIZER BAR(4-40 INSERT/BRDLOCK)
PLATING OPTIONS _____
1 = GOLD FLASH

SPECIFICATIONS:
MATERIALS:
SHELL: STEEL, TIN PLATED
INSULATOR: UL 94V-0 RATED PBTP
GLASS-FIBER REINFORCED
ELECTRICALS:
INDIVIDUAL CAPACITOR VALUE = 1000 pF
OTHER VALUES AVAILABLE: CONSULT FACTORY
CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: <10 mOHMS
INSULTOR RESISTANCE: 1000 OHMS
VOLTAGE: 1 KV / AC
TEMPERATURE: -55°C TO +125°C

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

CHECKED:

SCALE:
1:1

DWG NO.

DATE:
9-06-98

DATE:

SHEET
1 OF 1

REV
0

479-YYY-112RYY1