






TOP VIEW




RECOMMENDED PCB LAYOUT



BOTTOM VIEW



RECOMMENDED MOUNTING HOLE



1. MAX. PANEL THICKNESS=3.18mm

5	HEX. NUT	BRASS	GOLD	
4	LOCK WASHER	BRASS	GOLD	
3	CONTACT PIN	BER. COPPER	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BRASS	GOLD	1
DESCRIPTION	MATERIAL	FINISH	QTY	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	10/26/10
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/CONNEX/132416.DWG

Amphenol Connex			
PART DESCRIPTION			
SMA END LAUNCH RECEPT. JACK (.074" BOARD THICKNESS)			
PART NO.			
132416			
DWG. NO.	132416.DWG	REV.	NC
SIZE	A	SCALE	NA