
(5,00 mm) .197"
GRF1-C SERIES



50Ω GANGED MICRO-MINI RF CABLE

SPECIFICATIONS

For complete specifications see www.samtec.com?GRF1-C

Shell Material:
Brass
Insulator Material:
PTFE
Contact Material:
BeCu
Pin Material:
Brass
Plating:
30µ" (0,76 µm) Au over
50µ" (1,27 µm) Ni
Operating Temp Range:
-40°C to +90°C
Impedance:
50Ω
RoHS Compliant:
Yes

RG 316 Cable:

Impedance:
50Ω
Capacitance:
96.432 pF/meter
Propagation Delay:
4.83 nsec/meter
Max Attenuation (cable only):
1.25dB @ 1GHz for 1 meter
Conductor Size:
26 AWG, (0,51 mm) .020" dia.
Conductor Material:
Silver Plated Copper
Insulator Diameter:
(1,52 mm) .060"
Insulator Material:
PTFE
Shield Material:
Silver Plated Copper Clad Steel
Jacket Material:
FEP
Jacket Diameter:
(2,54 mm) .100"
Jacket Color:
Amber
RoHS Compliant:
Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594

Note:
Cable lengths longer than 40.00" (1 meter) are not supported with S.I. test data.

Note:
This Series is non-standard, non-returnable.


Mates with:
GRF1-J

TOOLING


Application Tooling.
Contact atg@samtec.com for more information.

OTHER SOLUTIONS

• 50Ω Board-to-Board system (see GRF1-J & GRF1-P Series)



GRF1	P	C	NO. OF POSITIONS	ASSEMBLED LENGTH	C1	END OPTION	SCREW OPTION
			–02, –04, –06, –08	–"XXXX" = Assembled Length in millimeters –0100 to –1000 (100 mm) 3.94" minimum		–S = Single –D = Double	–S = Captive Panel Screws (Leave blank for no Screw Option)



Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904858 SAMTEC KOREA • Tel: +82 31 717 5685