

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35098-9802](#)
Status: **Active**
Overview: [Quick-Disconnect Terminals](#)
Description: MP-Lock™ Quick Disconnect with Vibration Support, Female, for 16-20 AWG (1.30-0.50mm²), Metal Strip, Tab 5.20 x 0.51mm, Pre-Tin Plated

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35097-001 \(PDF\)](#)
[Packaging Specification PK-35098-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	35098
Crimp Quality Equipment	Yes
Insulated	No
Overview	Quick-Disconnect Terminals
Product Name	MP-Lock™
Type	Quick Disconnect
UPC	800754898089

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Net Weight	388.200/mg
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	5.21mm
Temperature Range - Operating	-40°C to +120°C
Wire Insulation Diameter	3.40mm max.
Wire Size AWG	16, 18, 20
Wire Size mm ²	0.50 - 1.30


Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35098-001
Product Specification	PS-35097-001
Sales Drawing	SD-35098-9*02



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35098Series](#)

Use With
5.21mm Tab

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan	
Description	Product #
End-Feed Applicator	0573823100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35098-9802