


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A ^{±.020}	W ^{±.010}	C ^{±.015}	M ^{±.020}	H ^{±.010}
P14-5SLF	#5	.51 (12.95)	.25 (6.35)	.22 (5.59)	.39 (9.91)	.12 (3.05)
P14-6SLF	#6	.51 (12.95)	.25 (6.35)	.22 (5.59)	.39 (9.91)	.14 (3.56)
P14-8SLF	#8	.56 (14.22)	.29 (7.37)	.25 (6.35)	.44 (11.18)	.16 (4.06)
P14-10SLF	#10	.57 (14.48)	.33 (8.38)	.25 (6.35)	.44 (11.18)	.19 (4.83)
P14-14SLF	1/4"	.66 (16.76)	.44 (11.18)	.35 (8.89)	.50 (12.70)	.25 (6.35)

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
A. #16-14 AWG SOLID OR STRANDED
COPPER WIRE
2. MATERIAL:
A. STAMPING - .03" (.76) THK COPPER,
TIN PLATED
3. PACKAGE QTY: STD. PKG. 100
BULK PKG. 1000
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS:

A. UL LISTED AND CSA CERTIFIED: CT-100,
CT-200, CT-570, CT-1570
B. PANDUIT APPROVED: CT-160, CT-260



LISTED
587H



CERTIFIED
LR31212

A41243_00

								P PANDUIT CORP. TINLEY PARK, ILLINOIS			
00	5/99	JKD		RELEASED				#16-14 BARREL NON-INSULATED SHORT LOCKING FORK			
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	APP	DRAWN BY DAW	CHK'D	SCALE NONE	DRAWING NO. A41243