

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
GDIST
14

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REV PER 0G3A-0092-03	03FEB03	JR	TM

AMP WIRE RANGE	 FILE E66717	 LR7189 Certified
16-14 AWG STRANDED	16-14 AWG STRANDED	16-14 AWG STRANDED

① MARKED AMP 16-14

2 DESIGNED FOR WIRE
INSULATION DIA OF
.110-.165.③ MATES WITH .250±.003
BY .032±.001 THK TAB.④ BODY: BRASS, TIN PLATED
SLEEVE: VINYL, BLUE

5 RATED FOR 15 MAX AMPERE



100	LOOSE PIECE	8-696302-1
3500	ON TAPE	696302-2
1000	LOOSE PIECE	696302-1
QTY	PACKAGE TYPE	PART NO.


TYCO ELECTRONICS
CUSTOMER SERVICE SYSTEMFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWING
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
75°C [167°F]VOLTAGE RATING:
300V MAXCIRCULAR MIL AREA:
2,050-5,180
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

- ④

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .008
4 PLC ± -
ANGLES ± -
FINISH - ④DWN
JR RUTH 15MAR01
CHK
MS FEHER 15MAR01
APVD
T MICHIELUTTI 15MAR01
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT - Tyco Electronics Corporation
Harrisburg, PA. 17057NAME
RECEPTACLE, 250 SERIES, FASTON, BUDGET,
PRE-INSULATED, WIRE:16-14 AWGSIZE
A3
CAGE CODE
00779
DRAWING NO
C-696302
RESTRICTED TO
-

CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV F