




Electrical Properties:

Frequency Range: 902~928 MHz
Impedance: 50Ω nominal
VSWR: <2.0:1
Gain: 2 dBi
Radiation: Omni
Polarization: Vertical
Wave: ½ wave

Mechanical Properties:

Connector: **RPSMA Plug**
Material:
Whip: Wire (Black)
Base: Polyacetal(Black)
Connector: Brass with nickel plating(Black)
Operation Temp.: -20°C to +65°C
Storage Temp.: -30°C to +75°C

TOLERANCE		TITLE	900MHz RPSMA antenna		DATE	SHEET
.X						1 OF 1
.XX		UNIT	DWG. NO.	A09-HSM-7		A4
.XXX		in(mm)				
		SCALE	MaxStream, Inc.			
ANGLE		1 : 1				