





Heyco® Nylon Cable Clamps

- For clamping cable or tubing securely into place.
- Resist corrosion, salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification or testing.)
- All parts are size marked in inches and millimeters.
- Molded in black and natural. 94V-0 halogen free nylon available.
- See page 7-20 for Arrow Clips and Push-In Fasteners suitable for securing Heyco Cable Clamps.

MOUNTING HOLE DIAMETER		SCREW SIZE	PART DIMENSION A		Black	PART NO.		94V-0 Halogen Free *	DESCRIPTION
in.	mm.		in.	mm.		Natural			
Light Duty - 3/8" (9,5 mm) Wide, .05" (1,3 mm) Thick									
.170	4,3	8	.125	3,2	3362	3312	-	CCL 125-170	
			.187	4,7	3363	3313	-	CCL 187-170	
			.250	6,3	3364	3314	-	CCL 250-170	
			.312	7,9	3365	3315	-	CCL 312-170	
			.375	9,5	3366	3316	-	CCL 375-170	
			.437	11,1	3367	3317	-	CCL 437-170	
			.500	12,7	3368	3318	-	CCL 500-170	
.203	5,2	10	.125	3,2	3352	3302	3373	CCL 1/8	
			.187	4,7	3353	3303	3374	CCL 3/16	
			.250	6,3	3354	3304	3375	CCL 1/4	
			.312	7,9	3355	3305	3376	CCL 5/16	
			.375	9,5	3356	3306	3377	CCL 3/8	
			.437	11,1	3357	3307	3378	CCL 7/16	
			.500	12,7	3358	3308	3379	CCL 1/2	
Heavy Duty - 1/2" (12,7 mm) Wide, .06" (1,5 mm) Thick									
.203	5,2	10	.125	3,2	3372	3322	-	CCH 1/8	
			.187	4,7	3373	3323	-	CCH 3/16	
			.250	6,3	3374	3324	-	CCH 1/4	
			.312	7,9	3375	3325	-	CCH 5/16	
			.375	9,5	3376	3326	-	CCH 3/8	
			.437	11,1	3377	3327	-	CCH 7/16	
			.500	12,7	3378	3328	-	CCH 1/2	
.203	5,2	10	.562	14,3	3379	3329	-	CCH 9/16	
			.625	15,9	3380	3330	-	CCH 5/8	
			.687	17,4	3381	3331	-	CCH 11/16	
			.750	19,1	3382	3332	-	CCH 3/4	
			.812	20,6	3383	3333	-	CCH 13/16	
			.875	22,2	3384	3334	-	CCH 7/8	
			1.000	25,4	3390	3340	-	CCH 1	
.203	5,2	10	1.125	28,6	3392	3342	-	CCH 1-1/8	
			1.187	30,1	3393	3343	-	CCH 1-3/16	
			1.250	31,8	3394	3344	-	CCH 1-1/4	
			1.375	34,9	3396	3346	-	CCH 1-3/8	
			1.500	38,1	3398	3348	-	CCH 1-1/2	



Standard colors black and natural.

*Consult Heyco for other sizes in 94V-0 halogen-free material.

Quick Specs

Material	6/6 Nylon
Certifications	UL Recognized under the Component Program of Underwriters' Laboratories File E54523
Flammability Rating	94V-2
Material Temperature Index	185°F (85°C) except select cable clamps molded in halogen-free 94V-0 Nylon